





SPECIFICATIONS

Current Rating: 1.5 Amps
Insulation Resistance: 1000M Ω , Min
Contact Resistance: 20m Ω , Max
Withstanding Voltage: AC 500V
Operation Temperature: -40° to +105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester (UL 94V-0)
Contact Plating: Gold Flash
Max. Processing Temp: 240° C for 30-60 seconds
(260° C for 5 seconds)



QTY	6	8	10	12	14	16	18	20	22
QTY	24	26	28	30	32	34	36	38	40
QTY	42	44	46	48	50	52	54	56	58
QTY	60	62	64	66	68	70			



深圳市韩下电子有限公司

UNLESS OTHERWISE SPECIFIED TOLERANCE

X : ±0.3 X° : ±5°
X.X : ±0.2 X.X° : ±1°
X.XX : ±0.1 X.XX° : ±0.5°

DRAWN NAME:

HX JN2.0-2x3P TP H6.4

SIZE	A4	SCALE	N:1	PROUCT NO.
REV	A	UNIT	mm	PROJECT

DRAW: 黄彬 2022/04/21 CHECKED: 张伟 2022/04/21 APPROVED: 罗小春 2022/04/21