


1 2 3 4 5 6 7 8 9

G



F

E

D




C

B

A

SPECIFICATIONS

Current Rating: 1.5 Amps
 Insulation Resistance: 1000M Ω , Min
 Contact Resistance: 20m Ω , Max
 Withstanding Voltage: AC 500V
 Operation Temperature: -40° to +105°
 Contact Material: Brass
 Standard: PA6T
 Insulator Material: Polyester (UL 94V-0)
 Contact Plating: Gold Flash
 Max. Processing Temp: 240° C for 30–60 seconds
 (260° C for 5 seconds)



RECOMMEND P. C. B. LAYOUT
PCB TOLERANCE: ±0.05 (TOP VIEW)

No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B
6	4.00	8.60	24	22.00	26.60	42	40.00	44.60	60	58.00	62.60
8	6.00	10.60	26	24.00	28.60	44	42.00	46.60	62	60.00	64.60
10	8.00	12.60	28	26.00	30.60	46	44.00	48.60	64	62.00	66.60
12	10.00	14.60	30	28.00	32.60	48	46.00	50.60	66	64.00	68.60
14	12.00	16.60	32	30.00	34.60	50	48.00	52.60	68	66.00	70.60
16	14.00	18.60	34	32.00	36.60	52	50.00	54.60	70	68.00	72.60
18	16.00	20.60	36	34.00	38.60	54	52.00	56.60			
20	18.00	22.60	38	36.00	40.60	56	54.00	58.60			
22	20.00	24.60	40	38.00	42.60	58	56.00	60.60			



深圳市韩下电子有限公司

UNLESS OTHERWISE SPECIFIED TOLERANCE		DRAWN NAME: HX JN2.0-2x5P WZ H6.4							
X	: ±0.30	X°	: ±5°	SIZE	A4	SCALE	N:1	PROUCT NO.	
X. X	: ±0.25	X. X°	: ±1°	REV	A	UNIT	mm	PROJECT	○
X. XX	: ±0.20	X. XX°	: ±0.5°	DRAW:	黄彬	2022/04/30	CHECKED:	张伟	2022/04/30 APPROVED: 罗小春 2022/04/30
									PAGE 1/1

1 2 3 4 5 6 7 8 9