



深圳市顺翔诺电子有限公司

SHENZHEN SHUNXIANGNUO ELECTRONICS CO., LTD.

客户名称:
Customer Name:

客户料号:
Customer P/N:

规格型号:
Specification Model:

顺翔诺品号:
SXN P/N:

制造商 Manufacturer		客户确认 Customer Approved	
制作 Drawn	何宇		
审核 Checked	江林平		
日期 Date	20240923	日期 Date	




SPECIFICATION FOR APPROVAL


地址:广东省深圳市龙华区观澜街道库坑社区新海洋工业园F栋2楼

ADD: 2 building F Building , New Ocean Industrial Park, Kukeng CommunityGuanlanStreet, Longhua District, Shenzhen City, Guangdong

电话Tel: +86-755-23760960 传真Fax: +86-755-28484866

E-mail:13713798056@163.com http://www.sxndz.com

CUSTOMER / 客户	SXN NO / 顺翔品号	UU9.8-5mH MIN		
1. MECHANICAL DIMENSIONS / 外形尺寸 [单位 mm]				
		SCHEMATIC / 原理图		
ITEM /项目	A	B	C	
SPEC /规格	11.5Max	16.5Max	17.5Max	
D	0.6±0.1	3.7±0.5	7.0±0.5	
E			8.0±0.5	
F				
G				
2. WINDING SPEC / 卷线规格				
WIRE /线材	0.32mm*1C 2UEW			
PIN /端子	1--2	4--3		
TURNS /圈数	48Ts (REF)	48Ts (REF)		
3. ELECTRICAL CHARACTERISTICS / 电气特性				
TEST ITEM / 测试项目	TEST WINDING /测试绕组	SPEC / 规格	CONDITION · EQUIPMENT /仪器·测试条件	
INDUCTANC /电感量	1--2 4--3	5mH MIN	CH-1062 or EQUIVALENT (F=1kHz, 0.25V)	
DCR /直流电阻	1--2 4--3	0.8 Ω MAX	CH-502A or EQUIVALENT (At25°C)	
INSULATION RESISTANCE / 绝缘电阻	COIL--COIL	100mΩ MIN	CH-19053 or EQUIVALENT At DC500V	
WITHSTAND VOLTAGE / 耐电压	COIL--COIL COIL--CORE	1.5KVAC 1.5KVAC	CH-19053 or EQUIVALENT (5mA/60sec)	
4. MATERIAL LIST / 材料明细表				
NO /编号	ITEM / 项目	MATERIAL /材料	SPEC / 规格	UL No / UL编号
1	BOBBIN /骨架	PHENOL /电木粉 T375J	SY-0901 or EQUIVALENT	E59481(S)
2	CORE /磁芯	FERRITE /铁氧体	JPH-7 UU9.8 or EQUIVALENT	
3	WIRE /线材	POLYURETHANE COPPER / 聚氨基甲酸酯铜线	0.32mm*1C 2UEW or EQUIVALENT	E194410
4	CLIP /夹子	STEEL /钢	UU9.8 or EQUIVALENT	
5	VARNISH /凡立水	EPOXY /环氧树脂	1032 or EQUIVALENT	E213437

CUSTOMER / 客户		SXN NO / 顺翔诺品号	UU9. 8-5mH MIN	
5. Product packaging / 产品包装 [单位 mm]				
EPE/ 珍珠棉: 340*240*10	TOP COVER/ 上盖: 345*245	INNER BOX/ 内盒: 345*245*30	OUTER BOX/ 外箱: 360*280*195	
				
NOTE/注:				
1. 成品采用针脚插珍珠棉包装方式每层420PCS放入一个内盒，共计420PCS。 The finished product is packaged with needle inserted pearl cotton, with 420PCS per layer placed in an inner box, for a total of 420PCS.				
2. 每三个内盒为一中包装，上层加纸板用封箱胶封成“#”字形为一个中包装。 Every three inner boxes form a central packaging, and the upper layer is sealed with cardboard and box glue in the shape of a "#" toform a central packaging.				
3. 每2个中包装为一箱，共计2520PCS。 Each box contains 2 packages, totaling 2520PCS.				
4. 外盒贴相应标签. 所有尺寸如上图。 Label the outer box accordingly. All dimensions are as shown in the above picture.				