





SPECIFICATIONS

Current Rating: 1.5 Amps
Insulation Resistance:1000M Ω , Min
Contact Resistance: 20m Ω , Max
Withstanding Voltage: AC 500V
Operation Temperature:-40° to+105°
Contact Material: Brass
Standard: PA6T
Insrlator Material: Polyester(UL 94V-0)
Contact Plating: Gold Flash
Max.Processing Temp: 240° C for30-60seconds
(260° C for5seconds)



lo. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B
6	4.00	8.60	24	22.00	26.60	42	40.00	44.60	60	58.00	62.60
8	6.00	10.60	26	24.00	28.60	44	42.00	46.60	62	60.00	64.60
10	8.00	12.60	28	26.00	30.60	46	44.00	48.60	64	62.00	66.60
12	10.00	14.60	30	28.00	32.60	48	46.00	50.60	66	64.00	68.60
14	12.00	16.60	32	30.00	34.60	50	48.00	52.60	68	66.00	70.6
16	14.00	18.60	34	32.00	36.60	52	50.00	54.60	70	68.00	72.60
18	16.00	20.60	36	34.00	38.60	54	52.00	56.60			
20	18.00	22.60	38	36.00	40.60	56	54.00	58.60			
22	20.00	24.60	40	38.00	42.60	58	56.00	60.60			



深圳市韩下电子有限公司

UNLESS OTHIEWIXE SPECIFIED TOLERANCE

X : ±0.3 X° : ±5°
X. X : ±0.2 X. X° : ±1°
X. XX: ±0.1 X. XX° : ±0.5°

DRAWM NAME: HX JN2.0-2x8P TP H6.4

SIZE	A4	SCALE	N:1	PROUCT NO.
REV	A	UNIT	mm	PROJECT

DRAW: 黄彬 2022/04/21 CHECKED: 张伟 2022/04/21 APPROVED: 罗小春 2022/04/21