



RECOMMENDED P.C.B LAYOUT (TOP VIEW)
TOLERANCES: $\pm 0.10\text{mm}$

TOLERANCE TABLE

.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	C _{km} tw 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD						
CHECKED:	DATE:	TITLE: DMRC-37P 公头 弯插 车针 铆合锁螺丝 全金 折弯7.2 带黑胶挡板						
DRAWN: LYF	DATE: 2018-04-07	CLIENT P/N					D-DMRC37PM-E001	
		UNIT	mm	SCALE	free			
		FILE NO.	Ckmtw-DMRC-0004			REV.	A	

parts no.	DIM. a	DIM. b	inner threac
B,C	4.8	11.8	4#40
D,E	5.8	12.0	4#40

SPECIFICATION
MATERIAL & FINISHES
INSULATOR: PBT GLASS FILLED UL94V-0
CONTACT: BRASS
SHELL : STEEL
PLATING : CONTACT GOLD FLASH PLATED

ELECTRICAL
Operation voltage: 250 VAC max.
Current rating: 3 Amps max.
Contact resistance: 15 mohms max.
Insulation resistance: 3000 Mohms min @ 500 VDC
Dielectric withstanding voltage: 1000 VAC / minute
Operating temperature: -55°C TO +105°C