

1		2		3		4		5		6		7		8																																																																																																															
SAMZO REAC/ROHS																																																																																																																													
										REV		ECN NO		DESRIPTION		DESIGN		APPROVAL		DATE																																																																																																									
												A1		NEW		Replace frame				2018.06.12																																																																																																									
E											technical parameters →.Impedance: 50Ω →.Frequency range: 0 - 12.4G →.Voltage standing wave ratio: For straight flexible cable, less than 1.15±0.02f (GHz) →.Operating voltage: 335V max →.Dielectric withstand voltage: 1000Vrms →.Contact resistance: Inner conductor less than 3 mOhm, outer conductor less than 2 mOhm →.Insulation resistance: greater than 500 MΩ →.Durability: 500 times →.Operating temperature: -65 to +165 (For PE CABLE, -40 to +85) →Standards: MIL-C-39012, IEC169-15, CECC22110																																																																																																																		
D																																																																																																																													
C																																																																																																																													
B	SMA-KWE-200-W4-0 Surface treatment镀层:普金 Pin position脚位:W4-正脚4pin Length体长:23mm Product number编号:KWE Product series系列:SMA同轴射频天线座										螺母垫片配件 PCB LAYOUT																																																																																																																		
A	<table><tr><th>ITEM</th><th>DESCRIPTION</th><th>MATERIAL</th><th>QTY</th><th>FINSH/COLOR</th><th colspan="4"></th><th colspan="4">FIRST VIEW</th><th colspan="4">The copyright belongs to samzo parts [China] Co., Ltd. please use the material after samzo parts agree to authorize. The final right of interpretation belongs to samzo parts. WWW.KKK-JP.COM</th><th colspan="2">TITLE:: SMA-KWE 20MM正脚4P 卧插</th></tr><tr><td>C</td><td>插孔</td><td>HPB59-1</td><td>1</td><td>_____</td><td colspan="4"></td><td colspan="4"></td><td colspan="4"></td><td colspan="2">DWG NO: SMAKWE200-P130</td></tr><tr><td>B</td><td>绝缘体</td><td>聚四氟乙烯</td><td>1</td><td>_____</td><td colspan="4">GENERAL TOLERANCE</td><td>SCALE</td><td>1:1</td><td>UNIT</td><td>mm</td><td colspan="4">PART NO: SMAKWE-2109301</td></tr><tr><td>A</td><td>主体</td><td>黄铜</td><td>1</td><td>镀金</td><td>DESIGN</td><td>WANGGUIFA</td><td>2018.06.12</td><td>≥2~5<</td><td>±0.25</td><td colspan="4">SAMZO COMPONENTS</td><td colspan="4">MODEL NO: SMA-KWE-200-W4-0</td></tr><tr><td></td><td></td><td></td><td></td><td></td><td>CHECKED</td><td>ZHENGUILAN</td><td>2018.06.12</td><td>≥0~2<</td><td>±0.15</td><td colspan="4">Electronic switch and connector manufacturer</td><td colspan="4">NAME: SMA</td></tr><tr><td></td><td></td><td></td><td></td><td></td><td>APPROVED</td><td>LILIANJIANG</td><td>2018.06.14</td><td>≥5</td><td>±0.35</td><td colspan="4"></td><td colspan="4">COAXIAL RF CONNECTOR</td></tr></table>										ITEM	DESCRIPTION	MATERIAL	QTY	FINSH/COLOR					FIRST VIEW				The copyright belongs to samzo parts [China] Co., Ltd. please use the material after samzo parts agree to authorize. The final right of interpretation belongs to samzo parts. WWW.KKK-JP.COM				TITLE:: SMA-KWE 20MM正脚4P 卧插		C	插孔	HPB59-1	1	_____													DWG NO: SMAKWE200-P130		B	绝缘体	聚四氟乙烯	1	_____	GENERAL TOLERANCE				SCALE	1:1	UNIT	mm	PART NO: SMAKWE-2109301				A	主体	黄铜	1	镀金	DESIGN	WANGGUIFA	2018.06.12	≥2~5<	±0.25	SAMZO COMPONENTS				MODEL NO: SMA-KWE-200-W4-0									CHECKED	ZHENGUILAN	2018.06.12	≥0~2<	±0.15	Electronic switch and connector manufacturer				NAME: SMA									APPROVED	LILIANJIANG	2018.06.14	≥5	±0.35					COAXIAL RF CONNECTOR									
ITEM	DESCRIPTION	MATERIAL	QTY	FINSH/COLOR					FIRST VIEW				The copyright belongs to samzo parts [China] Co., Ltd. please use the material after samzo parts agree to authorize. The final right of interpretation belongs to samzo parts. WWW.KKK-JP.COM				TITLE:: SMA-KWE 20MM正脚4P 卧插																																																																																																												
C	插孔	HPB59-1	1	_____													DWG NO: SMAKWE200-P130																																																																																																												
B	绝缘体	聚四氟乙烯	1	_____	GENERAL TOLERANCE				SCALE	1:1	UNIT	mm	PART NO: SMAKWE-2109301																																																																																																																
A	主体	黄铜	1	镀金	DESIGN	WANGGUIFA	2018.06.12	≥2~5<	±0.25	SAMZO COMPONENTS				MODEL NO: SMA-KWE-200-W4-0																																																																																																															
					CHECKED	ZHENGUILAN	2018.06.12	≥0~2<	±0.15	Electronic switch and connector manufacturer				NAME: SMA																																																																																																															
					APPROVED	LILIANJIANG	2018.06.14	≥5	±0.35					COAXIAL RF CONNECTOR																																																																																																															
1		2		3		4		5		6		7		8																																																																																																															