


	REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.05.09	







规格 Specification:

- 1.额定值 Rating:3A 125/250VAC
- 2.接触电阻 Contact resistance: $\leq 30\text{ m}\Omega$
- 3.绝缘电阻 Insulation resistance: $\geq 100\text{ M}\Omega$ (DC500V/Min)
- 4.电气寿命 Electronics life: $> 10000\text{ cycles}$
- 5.操作力 Operation force: $400\pm 150\text{ gf}$
- 6.所有材料符合RoHS要求 All materials are RoHS compliant

PART NO.:

$$\frac{\text{SS-X}}{\textcircled{1}} \quad \frac{03}{\textcircled{2}} \quad \frac{25}{\textcircled{3}} \quad \frac{\text{P}}{\textcircled{4}} \quad \frac{\text{G-XX}}{\textcircled{5}} \quad \frac{\text{N}}{\textcircled{6}} \quad \frac{3}{\textcircled{7}} \quad \frac{\text{X}}{\textcircled{8}} \quad \frac{\text{X}}{\textcircled{9}}$$

- ① SS: 立式拨柄开关;
② X: A:金属外壳;
BLANK: 塑胶外壳;
③ O3: 额定值3A;
④ 25: 双排五档;
⑤ P: 焊板端子;
⑥ G: 弧形拨柄;
⑦ XX: 拨柄高度H: 3~15mm;
⑧ N: 方形外壳;
⑨ 1: 端子焊脚规格TYPE-1; 2: 端子焊脚规格TYPE-2;
3: 端子焊脚规格TYPE-3; 4: 端子焊脚规格TYPE-4;
5: 端子焊脚规格TYPE-5;
⑩ X: 拨柄颜色: B-黑色; W-白色; R-红色
⑪ X: 主体颜色: B-黑色; W-白色; R-红色



产品字码标识

ANGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	



DESIGN	桑 葚	VIEW:		MODEL TYPE: SLIDE SWITCH		
CHECKED		UNIT: mm/in		PART NO.: SS-0325PG-XXN3XX		
APPROVED		SIZE: A4		DWG NO.:		
PRECISION CO.,LIMITED				SCALE	PAGE	REVISION
				N/A	1/1	A0

PCB LAYOUT

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	1/1	A0