

1



2

3

4

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.05.09	



A



规格 Specification:

- 额定值 Rating: 3A 125/250VAC
- 接触电阻 Contact resistance: $\leq 30 \text{ m}\Omega$
- 绝缘电阻 Insulation resistance: $\geq 100 \text{ M}\Omega$ (DC500V/Min)
- 电气寿命 Electronics life: > 10000 cycles
- 操作力 Operation force: $500 \pm 150 \text{ gf}$
- 所有材料符合Rohs要求 All materials are Rohs compliant

B




PART NO.:


SS-X 03 24 P G-XX N 1 X X
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩ ⑪

- ① SS: 立式拨柄开关;
② X: A: 金属外壳;
BLANK: 塑胶外壳;
③ 03: 额定值3A;
④ 24: 双排四档;
⑤ P: 焊板端子;
⑥ G: 弧形拨柄;
⑦ XX: 拨柄高度H: 3~15mm;
⑧ N: 方形外壳;
⑨ 1: 端子焊脚规格TYPE-1; 2: 端子焊脚规格TYPE-2;
3: 端子焊脚规格TYPE-3; 4: 端子焊脚规格TYPE-4;
5: 端子焊脚规格TYPE-5;
⑩ X: 拨柄颜色: B-黑色; W-白色; R-红色
⑪ X: 主体颜色: B-黑色; W-白色; R-红色

C



产品字码标识



D

PCB LAYOUT

ANGULAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	



DESIGN	桑 菴	VIEW:		MODEL TYPE:	SLIDE SWITCH
CHECKED		UNIT:	mm/in	PART NO.:	SS-0324PG-XXN1XX
APPROVED		SIZE:	A4	DWG NO.:	
XKB INDUSTRIAL PRECISION CO., LIMITED			SCALE	PAGE	REVISION
			N/A	1/1	A0

1

2

3

4