




电 路 图



PCB. 焊接图

$$\begin{array}{cccccccc} \text{J} & 4 & A & 050 & 1 & 1 & 1 & 0 \\ \hline \text{A} & \text{B} & \text{C} & \text{D} & \text{E} & \text{F} & \text{G} & \text{H} \end{array}$$

- A. 系列:L-6. 2*6. 2mm硅胶柄
B. 贴装方式:4-立式贴片
C. 引脚规格:A-2PIN
D. 操作高度:050-5. 0mm
E. 操作力度:1-260gf
F. 操作寿命:1-100, 000/次
G. 固定方式:1-无住
H. 物料编码:0-常规



5	引脚、触点	黄铜	1	镀银
4	底座	PPA	1	耐温280℃
3	簧片	不锈钢	1	覆银
2	盖板	不锈钢	1	/
1	按钮	硅胶	1	耐温280℃
序号	零件名称	材料规格	数量	备注


主要技术参数、性能

The Main Thchnology Performance

额定电流、电压 Rate voltage,current	50mA DC12V
接触电阻 Contact resistance	$\leq 50\text{m}\Omega$
按力 Operating force	$\pm 30\text{gf}$
行程 Travel	$0.25 \pm 0.10\text{mm}$
绝缘电阻 Insulated resistance	$\geq 100\text{M}\Omega$
介电强度 Dielectric strength	$\geq 250\text{VAC}/1\text{min}$

			GENERAL TOLERANCE	
			$\geq 0 \sim 2 <$	± 0.15
DESIGN	WANGGUIFA	2018.06.12	$\geq 2 \sim 5 <$	± 0.25
CHECKED	ZHENGUILAN	2018.06.12	$\geq 0 \sim 2 <$	± 0.15
APPROVED	LILIANJIANG	2018.06.14	≥ 5	$+0.35$

FIRST VIEW



The copyright belongs to samzo parts [China] Co., Ltd. please use the material after samzo parts agree to authorize. The final right of interpretation belongs to samzo parts.
WWW.KKK-JP.COM

TITLE:	
--------	--

6*6*5 两脚贴片 NEW

of DWG NO: J4A-P003

PART NO: J4A00019

MODEL NO: J4A0501110

NAME:

TACT SWITCH

SAMZO COMPONENTS
Electronic switch and connector manufacturer