



1 2 3 4 5 6 7 8 9


G




F



E



D



C

## SPECIFICATIONS

Current Rating: 1.5 Amps  
 Insulation Resistance: 1000M $\Omega$ , Min  
 Contact Resistance: 20m $\Omega$ , Max  
 Withstanding Voltage: AC 500V  
 Operation Temperature: -40° to +105°  
 Contact Material: Brass  
 Standard: PA6T  
 Insulator Material: Polyester (UL 94V-0)  
 Contact Plating: Gold Flash  
 Max. Processing Temp: 240° C for 30–60 seconds  
 (260° C for 5 seconds)



深圳市首韩科技有限公司

UNLESS OTHERWISE SPECIFIED TOLERANCE

X : ±0.30 X° : ±5°

X.X : ±0.25 X.X° : ±1°

X.XX : ±0.20 X.XX° : ±0.5°

DRAWN NAME: SH-JN2.0-2-7P-W

SIZE	A4	SCALE	N:1	PROJECT NO.
------	----	-------	-----	-------------

REV	A	UNIT	mm	PROJECT
-----	---	------	----	---------

DRAWN :	李春风	2020.6.24	CHECKED:	钟华华	2020.6.24	APPROVED:	罗孝金	2020.6.24
---------	-----	-----------	----------	-----	-----------	-----------	-----	-----------

No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B
6	4.00	6.00	24	22.00	24.00	42	40.00	42.00	60	58.00	60.00
8	6.00	8.00	26	24.00	26.00	44	42.00	44.00	62	60.00	62.00
10	8.00	10.00	28	26.00	28.00	46	44.00	46.00	64	62.00	64.00
12	10.00	12.00	30	28.00	30.00	48	46.00	48.00	66	64.00	66.00
14	12.00	14.00	32	30.00	32.00	50	48.00	50.00	68	66.00	68.00
16	14.00	16.00	34	32.00	34.00	52	50.00	52.00	70	68.00	70.00
18	16.00	18.00	36	34.00	36.00	54	52.00	54.00			
20	18.00	20.00	38	36.00	38.00	56	54.00	56.00			
22	20.00	22.00	40	38.00	40.00	58	56.00	58.00			

RECOMMEND P. C. B LAYOUT

PCB TOLERANCE: ± 0.05 (TOP VIEW)

1

2

3

4

5

6

7

8

9