





PCB LAYOUT



未注公差/General tolerances(mm)													0.1/10
0~3	>3~6	>6~10	>10~18	>18~30	>30~50	>50~80	>80~120	>120~180	>180~250	>250~315	>315~400	>400~500	
±0.12	±0.18	±0.22	±0.26	±0.31	±0.37	±0.57	±0.80	±0.93	±1.05	±1.15	±1.60	±2.20	±2.50

文 管 中 心
研 发 专 用

2020.05.13

(仅限内部使用, 对外无效)

2	Pin	Copper	Sn Plated
1	Housing	PA66	UL94V-0
ITEM	NAME OF PART	MATERIAL	NOTES
UL 标准/UL Standard:		B	C
额定电压/电流/Rated Voltage(V)/Current(A)		300/15	300/10
IEC 标准/IEC Standard:			
过压类别/Overvoltage Category/污染等级/Pollution Degree		III/3	III/2
额定电压/电流/Rated Voltage(V)/Current(A)		/	320/20
额定脉冲电压(KV)/Rate Impulse Voltage(KV)		/	4
间距/Pitch(mm)/线数范围/Poles		5.0/N=02~24P	
使用温度范围/Operating temperature(°C)		-40~+105	
符合RoHS环保要求/Conform to RoHS		Yes	

MATERIAL: /		SURFACE: /	
MAT NO.: /		 宁波高松电子有限公司 NINGBO DEGSON ELECTRICAL CO., LTD	
STATUS: /			
APPD: LanChH 2020.05.13		NAME: 2EDGV-5.0-XXP-1Y-100A(H)	
CHKD:GongYZh 2020.05.13			
DRFT: YinDK 2020.05.13		DRAWING NO.: 10001957	
REV		TO	
ECN		SHEET	
DESCRIPTION		1/1	
DRFT		TYPE: CUSTOMER DRAWING	
DATE		SCALE: 2:1	
		SIZE: A4	
		mm (inch)	