

Specifications

备注(Remark)

1. 材料(MATERIAL)

胶芯: PA9T+30%G.F UL94V-0, 颜色: 黑色.

Housing:PA9T+30%G.F UL94V-0, Color:Black

端子: 青铜, 镍底30u"MIN, 表面镀普金

Contact: Bronze, GOLD PLATING OVER ALL

30u" MIN NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电流: 2 AMP

Raring Current:2 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance: 20 mΩ MAX.

绝缘阻抗: 1000 M Ω MIN.





Insulating Resistance:1000 MΩ MIN.

耐电压: AC 500V/分钟.

Withstanding Voltage:AC 500V/Minute.


温度范围: -40°C to $+105^{\circ}\text{C}$

Temperture Range: -40°C to $+105^{\circ}\text{C}$



Ordering Information

F240-12 06 A0 C MU B 2



				OPERATION		SCALE		Fit		YXCON 东莞市宇熙精密连接器有限公司 www.yxcon.com Dongguan Yuxi Electronic Co.,Ltd.		
				X.X	±0.25	UNIT		MM				
				X.XX	±0.20	SIZE	A4	DESIGN	李官淼2021.11.04	PART NO	F240-1206A0CMUB2	
				X.XXX	±0.10							
				Angle	±3°	SHEET	1/1	CHECK		TITLE	PH2.0*4.0 2*6P SMT;6.2 带内柱Φ0.9*1.0 U型 W=4.0 PA9T料 镀黄金 CAP+卷	
REV	DATE	SYMBOL	MODIFICATION DESCRIPTION	DIM	TOL	PROJ.		APPROVE		Customer No.		