


- Electrical :
- | | | |
|--|---------------|------|
| | UL | IEC |
| 1. Rated Voltage : | 300V | 250V |
| 2. Rated Current : | 8A | 7A |
| 3. Withstanding Voltage : | AC1600V/1Min; | |
| 4. Operating Temperature : | -40°C~+105°C; | |
| 5. RoHS Compliance; | | |
| 6. Safty Approval : | cULus CE | |
| 7. ★ " is the key quality control point. | | |



15EGTVC - 3.81 -XXP - X X - 00

① Sereies NO. ④ 1 Single Pitch
 2 Double Pitch

② Pitch ⑤ Color: 1 Grey
 2 Blue
 3 Black
 4 Green
 5 Orange
 6 Red
 7 Transparent
 8 Yellow
 9 White

⑥ Customer Request: 00--Standard

Total Pitch Tolerances in mm									Nominal dimension range in mm										⊥	≡	—	//		
over 0	over 30	over 53	over 70	over 90	over 115	over 150	over 250	over 350	over 0	over 30	over 53	over 70	over 90	over 115	over 150	over 200	over 250	over 320	over 0	over 10	all	over 0	over 100	over 150
to 30	to 53	to 70	to 90	to 115	to 150	to 250	to 350	to 500	to 30	to 53	to 70	to 90	to 115	to 150	to 200	to 250	to 320	to 10	to 10		to 100	to 150	to 150	
±0.18	±0.20	±0.25	±0.3	±0.35	±0.44	±0.60	±0.70	±0.85	±0.20	±0.25	±0.30	±0.35	±0.44	±0.55	±0.70	±0.80	±0.90	0.2	0.3	0.3	0.2	0.3	0.5	

				OPERATI ON	SCALE	Fi t		Yxcon 东莞市宇熙精密连接器有限公司			
				X. X	±0.25	UNIT		www.yxcon.com	Dongguan Yuxi Electronic Co.,Ltd.		
				X. XX	±0.20	SI ZE	A4	DESIGN	赵文品2024. 10. 10	PART NO	15EGTVC-3. 81-XXP-XX-00
				X. XXX	±0.10	SHEET	1/1	CHECK		TI TLE:	
				Angle	±3°	PROJ.	1/1	APPROVE		Cust omer No.	
REV	DATE	SYMBOL	MODIFI CATI ON DESCRI PTI ON								