




PCB Layout




SECTION A-A

Electrical :

	UL	IEC
1.Rated Voltage :	300V	320V
2.Rated Current :	15A	20A
3.Withstanding Voltage :	AC1600V/1Min.	
4.Operating Temperature :	-40 °C~+105°C	
5. RoHS Compliance		
6.Safty Approval :		
7." ★ " is the key quality control point.		



2EGTVC - 5.08 -XXP - X X - 100



① Series No. ④ 1 Single Pitch
 2 Double Pitch

② Pitch

⑤ Color: 1 Grey
2 Blue
3 Black
4 Green
5 Orange
6 Red
7 Transparent
8 Yellow
9 White

③ Poles

02	02Contacts
03	03Contacts
...	
24	24Contacts

⑥ Customer Request: 100--Standard

Total Pitch Tolerances in mm									Nominal dimension range in mm									$\perp$	$=$	$-$	$//$		
over to	over to	over to	over to	over to	over to	over to	over to	over to	over to	over to	over to	over to	over to	over to	over to	over to	over to	over to	over to	all	over to	over to	over to
0 30	30 53	53 70	70 90	90 115	115 150	150 250	250 350	350 500	0 30	30 53	53 70	70 90	90 115	115 150	150 200	200 250	250 320	0 10	over 10	all	0 100	100 150	150
0.18	0.20	0.25	0.3	0.35	0.44	0.60	0.70	0.85	0.20	0.25	0.30	0.35	0.44	0.55	0.70	0.80	0.90	0.2	0.3	0.3	0.2	0.3	0.5

				OPERATION		SCALE		Fit	东莞市宇熙精密连接器有限公司 www.yxcon.com Dongguan Yuxi Electronic Co.,Ltd.		
				X.X	±0.25	UNIT		MM			
				X.XX	±0.20	SIZE	A4	DESIGN	赵文品2024.10.10	PART NO	2EGTVC-5.08-XXP-XX-100
				X.XXX	±0.10						
				Angle	±3°	SHEET	1/1	CHECK		TITLE	
REV	DATE	SYMBOL	MODIFICATION DESCRIPTION	DIM	TOL	PROJ.		APPROVE		Customer No.	