




## SPECIFICATION

1. Rating: DC 12V 0.3A
2. Travel: 2 mm
3. Function: 2P4T
4. Contact Resistance:  $\leq 70\text{m}\Omega\text{MAX}$
5. Operating Force: 200gf-350gf
6. Life test: 10,000 cycles



电话 : 0769-82320511-867

P.C.B LAYOUT

|     |                   |                 |     |           |                                                                                                                                                    |         |    |                                                                                                                                                                                      |           |         |     |      |
|-----|-------------------|-----------------|-----|-----------|----------------------------------------------------------------------------------------------------------------------------------------------------|---------|----|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------|---------|-----|------|
|     |                   |                 |     |           | TOLERANCE<br>UNLESS SPECIFIED                                                                                                                      |         |    |                                                                                                                                                                                      |           |         |     |      |
|     |                   |                 |     |           | UP TO 5mm:±0.1                                                                                                                                     | ANGULAR | A0 | 2023.02.09                                                                                                                                                                           | 首次发行      |         | GYW |      |
|     |                   |                 |     |           | ABOVE 5mm:±0.2                                                                                                                                     | ±1°     | NO | DATE                                                                                                                                                                                 | REVISIONS |         | BY  | APPD |
| 5   | MK24D02 TERMINAL  | BRASS           | 1   | Ag PLATED | TITLE:MINI SLIDE SWITCH                                                                                                                            |         |    | UNIT : MM                                                                                                                                                                            | ROHS      | DWN     |     |      |
| 4   | MK22D10A SPRING   | PHOSPHOR COPPER | 2   | WASHING   | MODEL:MK-24D20G2-B T6.0                                                                                                                            |         |    | SCALE: 5:1                                                                                                                                                                           | COMPLIANT | CHK'D   |     |      |
| 3   | MK24D20 CASE T6.0 | PA10T           | 1   | BLACK     |  DONGGUANG HAOYU ELECTRONICS CO., LTD<br>皓宇 HOOYA 东莞市弘皓电子有限公司 |         |    |                                                                                                                                                                                      |           | APPD    |     |      |
| 2   | MK24D02 COVER     | SUS             | 1   | WASHING   |                                                                                                                                                    |         |    |                                                                                                                                                                                      |           |         |     |      |
| 1   | MK24D02 KNOB      | PA10T           | 1   | BLACK     |                                                                                                                                                    |         |    |                                                                                                                                                                                      |           |         |     |      |
| NO. | PART NAME         | MATERIAL        | QTY | FINISHING |                                                                                                                                                    |         |    | PRO.AGL:   |           | REV :A0 |     |      |