







SCHEMATIC



P.C.B LAYOUT



SPECIFICATION

- 1.Rating : DC12V 50mA.
- 2.Contact resistance: $\leq 50m\Omega$.
- 3.Insulation resistance: $\geq 100M\Omega$ (DC100V).
- 4.Withstanding voltage: 250VAC .
- 5.Operating Force: $250\pm 80gf$.
- 6.Travel: $0.5\pm 0.2mm$.
- 7.life test: 10,000 cycles.

H=5.2MM

					TOLERANCE UNLESS SPECIFIED							
					<1.5: $\pm 0.1mm$ >1.5~5.0: $\pm 0.25mm$ >5.0: $\pm 0.3mm$	ANGULAR $\pm 1^\circ$	A1	2024.7.9	$\triangle$ 增加底座高度尺寸		MLQ	
									REVISIONS		BY	APPD
5	TERMINAL	BRASS	4	Ag-Plated	TITLE: TACT SWITCH			UNIT : MM	ROHS	DWN		
4	CASE	PPA	1		MODEL: TS-1110U2A-052C-03			SCALE: 1:1	COMPLIANT	CHK'D		
3	REED	SUS	1	Ag-Plated						APPD		
2	COVER	SUS	1									
1	BUTTON	RUBBER	1									
NO.	PART	NAME	MATERIAL	QTY	FINISHING						PRO.AGL:  	REV :A1



DONGGUANG HAOYU ELECTRONICS CO., LTD
东莞市弘皓电子有限公司

REV :A1