








P.C.B LAYOUT



SCHEMATIC



SPECIFICATION

- 1.Rating : AC12V 50mA.
- 2.Contact resistance: $\leq 100m\Omega$.
- 3.Insulation resistance: $\geq 100M\Omega$ (DC250V).
- 4.Withstanding voltage: 250VAC .
- 5.Operating Force: $250\pm 80gf$.
- 6.life test: 10,000 cycles.

					TOLERANCE						
					UNLESS SPECIFIED						
					<1.5: ±0.1mm >1.5~5.0: ±0.25mm >5.0: ±0.3mm	ANGULAR ±1°	A0	2024.7.19	首次发行		YKH
5	LED		1	ORANGE			NO	DATE	REVISIONS		BY APPD
4	CONTACT	PHOSPHOR BRONZE	1	Ag-PLATED	TITLE: TACT SWITCH			UNIT : MM	ROHS	DWN	
3	TERMINAL	BRASS STRIP	1	Ag-PLATED	MODEL: TC-1196A-L-E-01			SCALE: 1:1	COMPLIANT	CHK'D	
2	CASE	PA6T	1	BLACK	 DONGGUANG HAOYU ELECTRONICS CO., LTD 东莞市弘皓电子有限公司			APPD			
1	KNOB	PA66	1	WHITE							
NO.	PART	NAME	MATERIAL	QTY	FINISHING			PRO.AGL:			REV :A0