










H=4.3 5.0mm



电路图



PCB. 焊接图

SPECIFICATION

- 1.Rating : DC12V 50mA.
- 2.Contact resistance: $\leq 100m\Omega$.
- 3.Insulation resistance: $\geq 100M\Omega$ (DC100V).
- 4.Withstanding voltage: 250VAC .
- 5.Operating Force: $160\pm 50gf$ $250\pm 80gf$
- 6.Travel: $0.3\pm 0.1mm$.
- 7.life test: 100,000 cycles.
- 8.Operation temperature range: $-25^{\circ}C\sim 85^{\circ}C$.
- 9.Sign"* "is importance dimension.

					TOLERANCE UNLESS SPECIFIED								
					<1.5: ±0.1mm >1.5~5.0: ±0.25mm >5.0: ±0.3mm	ANGULAR ±1°	A0	2024.3.25	首次发行		ZLK	GYW	
5	CONTACT	BRASS	1	Ag-PLATED			NO	DATE	REVISIONS		BY	APPD	
4	CASE	PPA	1	BLACK	TITLE: TACT SWITCH			UNIT : MM		ROHS	DWN		
3	SPRING	SUS	1	Ag-Plated	MODEL: TC-06104FC-043E-R-03			SCALE: 1:1		COMPLIANT	CHK'D		
2	COVER	BRASS	1	Ni-PLATED	 DONGGUANG HAOYU ELECTRONICS CO., LTD 皓宇 东莞市弘皓电子有限公司						APPD		
1	KNOB	SILICA GEL	1	RED							PRO.AGL: 		REV :A0
NO.	PART	NAME	MATERIAL	QTY	FINISHING								