



P.C.B. LAYOUT

8					TOLERANCE UNLESS SPECIFIED										
7															
6					UP TO 5mm: ±0.1	ANGULAR	1								
5					ABOVE 5mm: ±0.2	±1°	NO	DATE	REVISIONS				BY	APPD	
4	CONTACT	SUS	1	NATURAL	TITLE: SLIDE SWITCH				UNIT : MM	ROHS COMPLIANT	DWN				
3	TERMINAL	BRASS STRIP	4	Ag PLATED	MODEL: TC-1197不带灯				SCALE: 1:1		CHK'D				
2	CASE	PA66	1	BLACK	 HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司						APPD				
1	KNOB	PA66	1	WHITE											
NO.	PART	NAME	MATERIAL	QTY	FINISHING							PRO.AGL:			REV :A0