







SCHEMATIC



P.C.B LAYOUT



H	
3.5	3.8
4.3	4.5
5.0	5.5
6.0	6.5
.....	
10.0	10.5

SPECIFICATION

- 1.Rating : DC12V 50mA.
- 2.Contact resistance: ≤100mΩ.
- 3.Insulation resistance: ≥100MΩ (DC250V).
- 4.Withstanding voltage: 250VAC .
- 5.Operating Force: 160±50gf/250±80gf.
- 6.Travel:0.2±0.1mm.
- 7.life test: 10,000 cycles.

					TOLERANCE UNLESS SPECIFIED								
					<1.5: ±0.1mm >1.5~5.0: ±0.25mm >5.0: ±0.3mm	ANGULAR ±1°							
5	TERMINAL	BRASS	2	Ag-Plated			NO	DATE	REVISIONS			BY	APPD
4	CASE	PA6T	1	BLACK	TITLE: TACT SWITCH				UNIT : MM		ROHS	DWN	
3	REED	SUS	1	Ag-Plated	MODEL: TC-00204V-050E-03				SCALE: 1:1		COMPLIANT	CHK'D	
2	FRAME	SPCC	1	Sn-Plated	 DONGGUANG HAOYU ELECTRONICS CO., LTD 皓宇 东莞市弘皓电子有限公司						APPD		
1	KNOB	PA6T	1	BLACK									
NO.	PART	NAME	MATERIAL	QTY	FINISHING					PRO.AGL:  			REV :A0