



HAOYU

SPECIFICATION

1. Rating : DC12V 50mA.
2. Contact resistance: $\leq 50\text{m}\Omega$.
3. Insulation resistance: $\geq 100\text{M}\Omega$ (DC500V).
4. Withstanding voltage: 250VAC .
5. Operating Force: $160\pm 50\text{gf}$
6. Travel: $0.25\pm 0.1\text{mm}$.
7. life test: 10,000 cycles.
8. Operation temperature range: $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.



SCHEMATEC



P.C.B LAYOUT

H	
4.3	4.5
5.0	5.5
6.0	6.5
7.0	7.5
8.0	8.5
9.0	9.5
10.0	

电话 : 0769-82320511-867

					TOLERANCE UNLESS SPECIFIED								
					<1.5: ±0.1mm >1.5~5.0: ±0.25mm >5.0: ±0.3mm	ANGULAR ±1°	A0						
5	TERMINAL	BRASS	1	Ag-PLATED			NO	DATE	REVISIONS			BY	APPD
4	CASE	PPA	1	BLACK	TITLE: TACT SWITCH				UNIT : MM	ROHS	DWN		
3	SPRING	SUS	1	Ag-PLATED	MODEL: TC-00102-050C				SCALE: 1:1	COMPLIANT	CHK'D		
2	COVER	BRASS	1	Ni-PLATED	 DONGGUANG HAOYU ELECTRONICS CO., LTD 东莞市弘皓电子有限公司				APPD				
1	KNOB	PPA	1	BLACK					PRO.AGL:  		REV: A0		
NO.	PART NAME	MATERIAL	QTY	FINISHING									