







SCHEMATIC



P.C.B LAYOUT



TRAVEL: 0.25±0.1mm

					TOLERANCE UNLESS SPECIFIED								
6	LED	GAASP/GAP	1		UP TO 5mm:±0.1	ANGULAR							
5	COVER	PET	1		ABOVE 5mm:±0.2	±1°	NO	DATE	REVISIONS			BY	APPD
4	BUTTON	PA66	1		TITLE:TACT SWITCH				UNIT : MM	ROHS	DWN		
3	SRPING	PHOSPHOR BRONZE	1	Ag-PLATED	MODEL: TC-1193RB-RL-C-01				SCALE: 1:1	COMPLIANT	CHK'D		
2	CASE	PA66	1		 DONGGUANG HAOYU ELECTRONICS CO., LTD 皓宇 东莞市弘皓电子有限公司				APPD				
1	TERMINAL	BRASS	4	Ag-PLATED									
NO.	PART	NAME	MATERIAL	QTY	FINISHING					PRO.AGL: 		REV :A0	