





SPECIFICATIONS

Current Rating: 1.0 Amps
Withstanding Voltage: AC 500V
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Operation Temperature: -40° to +105°
Insulator Material: Polyester (UL94V-0)
Contact Material: Phosphor bronze
Standard: PA6T
Contact Plating: Gold Flash
Max. Processing Temp:
240°C for 30-60 seconds
(260°C for 5 seconds)



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE: ±0.05 (TOP VIEW)

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

P/N	PIN	DIM.A	DIM.B
B127V08-0B1P51-H43C35	1	0.00	1.27
B127V08-0B2P51-H43C35	2	1.27	2.54
B127V08-0B3P51-H43C35	3	2.54	3.81
B127V08-0B4P51-H43C35	4	3.81	5.08
B127V08-0B5P51-H43C35	5	5.08	6.35
B127V08-0B6P51-H43C35	6	6.35	7.62
B127V08-0B7P51-H43C35	7	7.62	8.89
B127V08-0B8P51-H43C35	8	8.89	10.16
B127V08-0B9P51-H43C35	9	10.16	11.43
.....			
B127V08-0B50P51-H43C35	50	(50-1)x1.27	(50)x1.27

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.X ±0.30	X.° ±5°	PART NO. B127V08-0BXP51-H43C35	TITLE: 1.27FH H4.3 1xNPin SMT W2.1 U型 PC3.5 PB4.6 6T(左前右后)		
.XX ±0.20	X.* ±1°				
.XXX ±0.10	X.XX*±0.5°	DESIGN: Ethan	MANUFACTURE DWG		
UNITS	mm	CHED: Olvia		SCALE	SHEET
MATERILA	— — —	APPD: Ava		N:A	1/1
FINISH	— — —				