





HAOYU

主要技术规格:

1. 额 定 值: 50mA DC12V
2. 接触电阻: $\leq 50m\Omega$
3. 操 作 力 E: $250 \pm 40gf$
4. 行 程: $0.20 \pm 0.1mm$
5. 绝缘电阻: $\geq 100M\Omega$
6. 抗电强度: 250V 50HZ 1Min.
7. 寿 命: 100,000 Cycles




CIRCUIT DIAGRAM



电话: 0769-82320511-867

操作力 E: $250 \pm 40gf$
H=5.5mm



P.C.B. LAND DIMENSION

				TOLERANCE UNLESS SPECIFIED							
				UP TO 5mm: ± 0.1	ANGULAR	A1	2022.11.7	更新图纸	WM		
				ABOVE 5mm: ± 0.2	$\pm 1^\circ$	NO	DATE	REVISIONS	BY	APPD	
5	STEM	PA66	1			TITLE: TACT SWITCH		UNIT: MM	ROHS COMPLIANT	DWN	
4	COVER	IRON	1	C.T-PLATED		MODEL: TC-00105-055E		SCALE: 1:1	CHK'D		
3	CONTACT	PHOSPHOR BRONZE	1	AG-PLATED						APPD	
2	TERMINAL	BRASS	1	AG-PLATED							
1	BASE	PA66	1	BLACK							
NO.	PART NAME	MATERIAL	QTY	FINISHING						PRO.AGL:	
										REV: A1	



DONGGUANG HAOYU ELECTRONICS CO., LTD
东莞市弘皓电子有限公司