







SCHEMATIC



P.C.B LAYOUT

H=4.3/5.0/5.3/5.8/6.0/6.3/7.3mm

SPECIFICATION

- 1.Rating : DC12V 50mA.
- 2.Contact resistance: $\leq 100\text{m}\Omega$.
- 3.Insulation resistance: $\geq 100\text{M}\Omega$ (DC250V).
- 4.Withstanding voltage: 250VAC .
- 5.Operating Force: $250\pm 80\text{gf}$
- 6.Travel: $0.2\pm 0.1\text{mm}$.
- 7.life test: 30000 cycles.

					TOLERANCE UNLESS SPECIFIED								
					<1.5: ±0.1mm >1.5~5.0: ±0.25mm >5.0: ±0.3mm	ANGULAR ±1°	1						
5	TERMINAL	BRASS	1	Ag-Plated			NO	DATE	REVISIONS			BY	APPD
4	CASE	PPA	1	Black	TITLE: TACT SWITCH				UNIT : MM	ROHS	DWN		
3	SHRAPNEL	SUS	1	Ag-Plated	MODEL: TS-1112AE-E-03				SCALE: 1:1	COMPLIANT	CHK'D		
2	COVER	BRASS	1	Sn-Plated	 DONGGUANG HAOYU ELECTRONICS CO., LTD 东莞市弘皓电子有限公司						APPD		
1	BUTTON	PPA	1	White									
NO.	PART	NAME	MATERIAL	QTY	FINISHING					PRO.AGL: 			REV :A0