





P.C.B LAYOUT



CIRCUIT



LED COLOR					
1	2	3	4	5	6
Red	Yellow	Green	Blue	White	Pure Green

NOTES:

- 1.RATING: 12VDC 50mA
- 2.CONTACT RESISTANCE: 100mΩ Max
- 3.INSULATION RESISTANCE: 100MΩ 250VDC FOR 1MIN
- 4.DIELECTRIC STRENGTH: 250VAC(50/60Hz) FOR 1MIN
- 5.LIFE TEST:100,000 CYCLES
- 6.OPERATION FORCE&TRAVEL: SEE SPECIFICATION

电话 : 0769-82310511-867

邮箱 : hooya89@hooya.hk

V : hooya89

					TOLERANCE UNLESS SPECIFIED						
					UP TO 5mm: ±0.1	ANGULAR	1				
					ABOVE 5mm: ±0.2	±1°	NO	DATE	REVISIONS	BY	APPD
					TITLE: TACT SWITCH			UNIT : MM	ROHS COMPLIANT	DWN	
					MODEL: TC-1198-L-E-C1			SCALE: 1:1	CHK'D		
					HAOYU(HONGKONG)LIMITED					APPD	
					皓宇(香港)有限公司					PRO.AGL:	REV :A0
NO.	PART	NAME	MATERIAL	QTY	FINISHING						