









P.C.B LAYOUT



CIRCUIT



DOT SHOWING LED
COLOR IS MARKED
FOR MINUS POLE
SEE SCHEMATIC



NOTES:

Electrical Characteristics:

Rating : 50mA 12VDC

Contact Resistance: 50mΩ max. (Initial)

Insulation Resistance: 100MΩ min. (at 250 VDC)

Dielectric Strength: AC 250V(50/60Hz) for 1 minute.

LED Operating Current: 20mA max.

Mechanical Characteristics:

Operating Force: 160±50gf

Travel: 0.25±0.1mm

Static load : 5Kg / 60 sec

Operating Life: 100,000 cycles min.

Operating temperature: -20°C to 70°C.


LED COLOR (X)

1	2	3	4	5	6	23	12	13	14	52	..
Red	Yellow	Green	Blue	White	Pure green	Yellow Green	Red Yellow	Red Green	Red Blue	White Yellow	..

电话 : 0769-82310511-867

邮箱 : hooya89@hooya.hk

V : hooya89

					TOLERANCE UNLESS SPECIFIED								
6	LED	GaAsp/GAP	1		UP TO 5mm:±0.1	ANGULAR	1						
5	TERMINAL	BRASS	4	Ag-PLATED	ABOVE 5mm:±0.2	±1°	NO	DATE	REVISIONS			BY	APPD
4	HOUSING	PA66	1		TITLE: TACT SWITCH			UNIT : MM		ROHS COMPLIANT	DWN		
3	CONTACT	SUS	1	Ag-PLATED	MODEL: TC-1194M-YW-D			SCALE: 1:1			CHK'D		
2	COVER	PBT	1		 HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司						APPD		
1	BUTTON	PA66	1								PRO.AGL: 		REV :A0
NO.	PART	NAME		MATERIAL	QTY	FINISHING							