






SPECIFICATIONS
Current Rating: 1.0 Amps
Withstanding Voltage: AC 500V
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Operation Temperature: -40° to +105°
Insulator Material: Polyester (UL94V-0)
Contact Material: Phosphor bronze
Standard: PA6T
Contact Plating: Gold Flash
Max. Processing Temp: 240°C for 30-60 seconds
(260°C for 5 seconds)



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE: ±0.05 (TOP VIEW)

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

P/N	PIN	DIM.A	DIM.B
B127M05-0B2P51-H43C48	2*1	0.00	1.27
B127M05-0B4P51-H43C48	2*2	1.27	2.54
B127M05-0B6P51-H43C48	2*3	2.54	3.81
B127M05-0B8P51-H43C48	2*4	3.81	5.08
B127M05-0B10P51-H43C48	2*5	5.08	6.35
B127M05-0B12P51-H43C48	2*6	6.35	7.62
B127M05-0B14P51-H43C48	2*7	7.62	8.89
B127M05-0B16P51-H43C48	2*8	8.89	10.16
B127M05-0B18P51-H43C48	2*9	10.16	11.43
.....			
B127M05-0B100P51-H43C48	2*50	(50-1)x1.27	(50)x1.27

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.X ±0.30	X.* ±5°	PART NO.	TITLE: 1.27FH H4.3 2xNPin		
.XX ±0.20	X.X* ±1°	B127M05-0BXP51-H43C48	SMT U型 PC4.8 PB4.6 6T		
.XXX ±0.10	X.XX* ±0.5°	DESIGN: Ethan	MANUFACTURE DWG		
UNITS	mm	CHED: Olivia			
MATERILA	— — —	APPD: Ava			
FINISH	— — —		SCALE	SHEET	
			N:A	1/1	