







SCHEMATIC



P.C.B LAYOUT



H	
3.5	3.8
4.3	4.5
5.0	5.5
6.0	6.5
.....	
10.0	10.5

SPECIFICATION

- 1.Rating: DC12V 50mA.
- 2.Contact resistance: $\leq 100m\Omega$.
- 3.Insulation resistance: $\geq 100M\Omega$ (DC100V).
- 4.Withstanding voltage: 250VAC.
- 5.Operating Force: $160\pm 50gf/250\pm 80gf$ (依客户需求而定).
- 6.Travel: $0.2\pm 0.1mm$.
- 7.Life test: 100,000 cycles.

					TOLERANCE UNLESS SPECIFIED											
					<1.5: ±0.1mm >1.5~5.0: ±0.25mm >5.0: ±0.3mm	ANGULAR ±1°	A0	2024.5.7	初次发行			TQF				
5	TERMINAL	BRASS	1	Ag-PLATED			NO	DATE	REVISIONS			BY	APPD			
4	HOUSING	PPA	1	BLACK	TITLE: TACT SWITCH				UNIT : MM		ROHS	DWN				
3	REED	SUS	1	Ag-PLATED	MODEL: TC-00204Z-070C-03				SCALE: 1:1		COMPLIANT	CHK'D				
2	COVER	SPCC	1	Sn-PLATED	 皓宇 HOUYA DONGGUANG HAOYU ELECTRONICS CO., LTD 东莞市弘皓电子有限公司						APPD					
1	KNOB	PPA	1	BLACK												
NO.	PART	NAME	MATERIAL	QTY							FINISHING					



DONGGUANG HAOYU ELECTRONICS CO., LTD
东莞市弘皓电子有限公司