



P.C.B LAYOUT

电话：0769-82320511-867




SCHEMATIC

皓宇电子
HOOYA ELECTRONICS

SPECIFICATION

1. Rating: DC 12V 0.3A
2. Travel: 2 mm
3. Function: 1P2T
4. Contact Resistance: $\leq 70\text{m}\Omega\text{MAX}$
5. Operating Force: $200\pm 80\text{gf}$
6. Life test: 10,000 cycles



KNOB X = 2, 2.5, 3, 4, 4.5mm

					TOLERANCE							
					UNLESS SPECIFIED		A1	2020.06.05	△ 新增局部剖视图, 定义胶柄装配方向		GYW	
					UP TO 5mm: ± 0.1	ANGULAR	A0	2017.06.08	首次发行		GYW	
					ABOVE 5mm: ± 0.2	$\pm 1^\circ$	NO	DATE	REVISIONS		BY	APPD
5	MK12D13 TERMINAL	BRASS	1	Ag PLATED/NATURAL	TITLE: MINI SLIDE SWITCH			UNIT : MM	ROHS COMPLIANT	DWN		
4	MK22D10 SPRING	PBS	1	NATURAL	MODEL: MK-12D13G2-B弹线环保			SCALE: 7:1	CHK'D			
3	MK12D13 KNOB	PA46	1	BLACK/WHITE/RED	HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司			APPD		PRO.AGL:		REV :A1
2	MK12D13 CASE	PA66/PA9T	1	BLACK								
1	MK12D13 COVER	0.2mm SUS	1	WASHING								
NO.	PART NAME	MATERIAL	QTY	FINISHING								