







H	L
3.3	2.80
3.8	
4.3	3.15
4.5	
5.0	
5.5	
7.0	



SCHEMATIC



P.C.B LAYOUT

SPECIFICATION

- 1.Rating : DC12V 50mA.
- 2.Contact resistance: $\leq 100\text{m}\Omega$.
- 3.Insulation resistance: $\geq 100\text{M}\Omega$ (DC250V).
- 4.Withstanding voltage: 250VAC .
- 5.Operating Force: $160\pm 50\text{gf}/250\pm 80\text{gf}$ (依客户需求而定) .
- 6.Travel: $0.3\pm 0.1\text{mm}$.
- 7.life test: 10,000 cycles.

TRAVEL:IP67

				TOLERANCE UNLESS SPECIFIED					
				<1.5: $\pm 0.1\text{mm}$	ANGULAR				
				>1.5~5.0: $\pm 0.25\text{mm}$	$\pm 1^\circ$				
				>5.0: $\pm 0.3\text{mm}$		NO	DATE	REVISIONS	BY APPD
6	TERMINAL	BRASS	4	Ag-Plated	TITLE: TACT SWITCH				
5	CASE	PPA	1	BLACK	UNIT : MM		ROHS	DWN	
4	REED	SUS	1	Ag-Plated	MODEL: TC-06104FSB-045E-R-03		COMPLIANT	CHK'D	
3	WATERPROOF PAD	RUBBER	1	BLACK	SCALE: 1:1			APPD	
2	COVER	SUS	1		DONGGUANG HAOYU ELECTRONICS CO., LTD				
1	BUTTON	PPA	1	RED/BLACK	东莞市弘皓电子有限公司				
NO.	PART	NAME	MATERIAL	QTY	FINISHING	PRO.AGL:  			
						REV :A0			