



SPECIFICATIONS

Current Rating:1.0 Amps
Withstanding Voltage:AC 500V
Insulation Resistance:1000MΩ Min
Contact Resistance:20mΩ Max
Operation Temperature:-40°to+105°
Insulator Material:Polyester(UL94V-0)
Contact Material:Brass
Standard:PA6T
Contact Plating:Gold Flash
Max.Processing Temp: 240°C for30-60seconds
(260°C for5seconds)


P/N	PIN	DIM.A	DIM.B
PH1.27-03-01PWD	1	0.00	1.27
PH1.27-03-02PWD	2	1.27	2.54
PH1.27-03-03PWD	3	2.54	3.81
PH1.27-03-04PWD	4	3.81	5.08
PH1.27-03-05PWD	5	5.08	6.35
PH1.27-03-06PWD	6	6.35	7.62
PH1.27-03-07PWD	7	7.62	8.89
PH1.27-03-08PWD	8	8.89	10.16
PH1.27-03-09PWD	9	10.16	11.43
.....			
PH1.27-03-50PWD	50	(PIN-1)x1.27	(PIN)x1.27



PART NUMBER DESCRIPTION:

PH1.27-03-NPVD

(D=单排;S=双排)
(Z=直脚;W=弯脚)
(PIN数量;01.....50PIN)
(排针开关)



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE:1.27PH H1.0 1xnPin SMT W2.0 PC4.3 PA4.0 PB1.5 L7.2 6T(左前右后)
			PAR PH1.27-03-NPVD
DECIMALS:	ANGLES:		DWN
X.±0.30	X°±5'		CHKD
X.X±0.20	X.X°±1'		APVD
X.XX±0.10	X.XX°±0.5'		SCALE N:A UNIT:MM
CUSTOMER COPY		SIZE:A4	SHEET:1F1 REV:A