





CIRCUIT DIAGRAM

P . C . B LAYOUT



SPECIFICATION

1. Rating : DC12V 50mA.
2. Contact resistance: $\leq 100\text{m}\Omega$.
3. Insulation resistance: $\geq 100\text{M}\Omega$ (DC100V).
4. Withstanding voltage: 250VAC .
5. Operating Force: $250 \pm 80\text{gf}$
6. Travel: $0.13 \pm 0.1\text{mm}$.
7. life test: 5,0000 cycles.

					TOLERANCE UNLESS SPECIFIED							
					UP TO 5mm: ± 0.1	ANGULAR $\pm 1^\circ$	A0	2024.7.10	首次發行		YKH	
					ABOVE 5mm: ± 0.2		NO	DATE	REVISIONS		BY	APPD
5	STEM	PA9T	1	BLACK	TITLE: TACT SWITCH			UNIT : MM	ROHS COMPLIANT	DWN		
4	DUSTPROOF FILM	PA9T	1	WHITE	MODEL: TS-1191-E			SCALE: 1:1		CHK'D		
3	CONTACT	SUS	2	Ag-PLATED	 DONGGUANG HAOYU ELECTRONICS CO., LTD 东莞市弘皓电子有限公司					APPD		
2	CASE	PA9T	1	BLACK								
1	TERMINAL	PHOSPHOR BRONZE	1	Ag-PLATED								
NO.	PART NAME	MATERIAL	QTY	FINISHING				PRO.AGL: 		REV :A0		