





NOTES:

备注

1. Copper, nickel base, matte tin

黄铜, 镍底, 镀雾锡

2. Wire screw hole M4

压线螺孔M4

3. Current Rating: 45A


额定电流: 45A

4. There shall be no defects such as pin deformation and burrs.

不得有脚变形, 毛刺等缺陷

5. Unmarked dimensions refer to tolerances

未标注的尺寸参考公差



Ordering Information

HC - * * * - * * * - D * * * * - 01

Type	Screw	Welding	Series	D=01P	Product No.	Material
M=Pull Teeth (铆钉)	3=M3 (螺牙)	Feet (焊脚)	0808=8x8mm 1620=16x20mm	S=SM FD=Flag Dip	产品序号	默认=Copper (黄铜) RC=Red Copper (紫铜)
R=Rivet Nut (铆螺母)	4=M4 (螺牙) 5=M5 (螺牙) 6=M6 (螺牙)	2=2个 4=4个 6=6个 8=8个				



GENERAL TOLERANCE

制 图

01

深圳市华灿天禄电子有限公司

ShenzhenhuacantianluELECTRONICS CO., LTD

DIM TOL

审 核

产品名称
TITLE
PCB 焊接端子 插板 铆垫片 M4
4焊脚 8x8x8.7mm

版 本
REV.
A

5 or more ±0.35

批 准

产品料号
PART NO.
HC-RG44-0808-D001RC-01

单 位
UNITS
mm

2~5 ±0.25

比 例

材料
MATERIAL

页 次
SHEET
1/1

0~2 ±0.15

SCALE

Angle ±3.0°

投 影



1

初版发行

序号

变更内容

日期

MODIFY DATE

工程专用章