



- 

深圳市华宇创精密电子有限公司


TOLERANCE:		DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME:	
X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X: ±2° X.X° ±0.5°				NGFF M.2 E KEY 4.8H 0.5PH	
 UNIT: mm [inch]		CHECKED BY:	DATE :	PART NO.	HYCW35E-05NGFF-480B
		马跃	2014-02-23	MOLD NO.	
				APPROVED BY:	DATE :
SCALE:1:1	SIZE: A4	邱敏	2014-02-23	SHEET NO.	1 OF 1




Stack-up Top Mount Double Sided Module for
1.20 max top-side component height



Stack-up Top Mount Double Sided Module for
1.35 max top-side component height



Stack-up Top Mount Double Sided Module for
1.50 max top-side component height



HOW TO MATE AND EXTRACT

MATE: ① → ④





EXTRACT: ⑤ $\longrightarrow$ ⑥

NOTE:Mating force will generate from step 3 to step 4.





深圳市华宇创精密电子有限公司

TOLERANCE:		DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME:	
X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X: ±2° X.X° ±0.5°				NGFF M.2 E KEY 4.8H 0.5PH	
 UNIT: mm [inch]		CHECKED BY:	DATE :	PART NO.	HYCW35E-05NGFF-480B
		马跃	2014-02-23	MOLD NO.	
				APPROVED BY:	DATE :
SCALE:1:1	SIZE: A4	邱敏	2014-02-23	SHEET NO.	1 OF 1







RECOMMENDED PCB LAYOUT(TOP VIEW)

DEFAULT TOLERANCE $\pm 0.05\text{MM}$



		深圳市华宇创精密电子有限公司			
TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X* ±2* X.X* ±0.5*		DRAWN BY : 陈一鸣		DATE : 2014-02-23	
		CHECKED BY: 马跃		PART NAME: NGFF M.2 E KEY 4.8H 0.5PH	
		DATE : 2014-02-23		PART NO. HCYW35E-05NGFF-480B	
		APPROVED BY: 邱敏		MOLD NO.	
UNIT: mm [inch]		DATE : 2014-02-23		DRAW NO: HYC-2205091027	
SCALE:1:1 SIZE: A4		SHEET NO.		1 OF 1	



900	5400
PCS/REEL	PCS/CARTON



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ± 0.30 X.XX ± 0.25 X.XXX ± 0.15 X.' $\pm 2'$ X.X' $\pm 0.5'$ UNIT: mm [inch] SCALE:1:1 SIZE: A4	DRAWN BY :	DATE :	PART NAME:	
	陈一鸣	2014-02-23	包装图	
	CHECKED BY:	DATE :	PART NO.	
	马跃	2014-02-23	MOLD NO.	
	APPROVED BY:	DATE :	DRAW NO:	
	邱敏	2014-02-23	SHEET NO.	1 OF 1