


- Electrical :
- | | | |
|---|----------------|------|
| | UL | IEC |
| 1.Rated Voltage : | 300V | 250V |
| 2.Rated Current : | 8A | 7A |
| 3.Withstanding Voltage : | AC1600V/1Min; | |
| 4.Operating Temperature : | -40 °C~+105°C; | |
| 5. RoHS Compliance; | | |
| 6.Safty Approval : | cULus | |
| 7." ★ " is the key quality control point. | | |



- 15EGTRC - 3. 81 -XXP - X X - 00
- | | | | | | |
|---------------|---------|---------|------------------------------------|--|----------------------------------|
| ① | ② | ③ | ④ | ⑤ | ⑥ |
| ① Sereies NO. | ② Pitch | ③ Poles | ④ 1 Single Pitch
2 Double Pitch | ⑤ Color: 1 Grey
2 Blue
3 Black
4 Green
5 Orange
6 Red
7 Transparent
8 Yellow
9 White | ⑥ Customer Request: 00--Standard |

Total Pitch Tolerances in mm										Nominal dimension range in mm										⊥	≡	—	//		
over 0 to 30	over 30 to 53	over 53 to 70	over 70 to 90	over 90 to 115	over 115 to 150	over 150 to 250	over 250 to 350	over 350 to 500		over 0 to 30	over 30 to 53	over 53 to 70	over 70 to 90	over 90 to 115	over 115 to 150	over 150 to 200	over 200 to 250	over 250 to 320		over 0 to 10	over 10 all	over 0 to 100	over 100 to 150	over 150	
±0.18	±0.20	±0.25	±0.3	±0.35	±0.44	±0.60	±0.70	±0.85	±0.20	±0.25	±0.30	±0.35	±0.44	±0.55	±0.70	±0.80	±0.90			0.2	0.3	0.3	0.2	0.3	0.5

				OPERATION	SCALE	Fit	Yxcon 东莞市宇熙精密连接器有限公司				
				X.X ±0.25	UNIT	MM	www.yxcon.com Dongguan Yuxi Electronic Co.,Ltd.				
				X.XX ±0.20	SIZE	A4	DESIGN	赵文品2024. 10. 15	PART NO.	15EGTRC-3. 81-XXP-XX-00	
				X.XXX ±0.10	SHEET	1/1	CHECK		TITLE:		
REV	DATE	SYMBOL	MODIFICATION DESCRIPTION	ANGLE ±3°	PROJ.		APPROVE		Customer No.		
				DIM TOL							