







- NOTES:
1. MATERIAL SPECIFICATION:
    - 1-1. HOUSING: LCP+40%GF  
UL94V-0, COLOR: BLACK.
    - 1-2. CONTACT: COPPER ALLOY.
    - 1-3. TAB: S50C.
  2. PLATING SPECIFICATION:
    - 2-1. CONTACT:  
50u" MIN.NICKEL UNDER PLATING OVER ALL.  
G/F PLATING ON SOLDER AREA.  
GOLD PLATING ON CONTACT AREA:SEE TABLE
    - 2-2. TAB:  
50u" MIN. NICKEL UNDER PLATING OVER ALL .  
80u" MIN. MATTE TIN PLATING ON SOLDER AREA.
  3. HF COMPLIANT.
  4. DATE CODE: XXXXXX  

  5. MECHANICAL PERFORMANCE:
    - 5-1. DURABILITY: 25 CYCLES.
  6. ELECTRICAL PERFORMANCE:
    - 6-1. CURRENT: 0.5A PER PIN.
    - 6-2. LLCR: INITIAL 55mΩ MAX.FINAL  $\Delta$ LLCR=20mΩ
  7. RESISTANCE TO HEAT:  
THE TEMPERATURE SHALL BE 260±5°C MAINTAINING  
10±1 SECONDS.





深圳市华宇创精密电子有限公司




|                                                                                       |          |                   |                      |                             |                    |
|---------------------------------------------------------------------------------------|----------|-------------------|----------------------|-----------------------------|--------------------|
| TOLERANCE:                                                                            |          | DRAWN BY :<br>陈一鸣 | DATE :<br>2014-02-23 | PART NAME:                  |                    |
| X.X ±0.30<br>X.XX ±0.25<br>X.XXX ±0.15<br><br>X.* ±2*    X.X* ±0.5*                   |          |                   |                      | NGFF M.2 M KEY 1.5H 沉板0.5PH |                    |
|  |          | CHECKED BY:       | DATE :               | PART NO.                    | HYCW13M-05NGFF-150 |
|                                                                                       |          | 马跃                | 2014-02-23           | MOLD NO.                    |                    |
| UNIT: mm [inch]                                                                       |          | APPROVED BY:      | DATE :               | DRAW NO:                    | HYC-2309111105     |
| SCALE:1:1                                                                             | SIZE: A4 | 邱敏                | 2014-02-23           | SHEET NO.                   | 1 OF 1             |



|                                                                                                          |  |                        |  |                            |  |                                                                                                |  |
|----------------------------------------------------------------------------------------------------------|--|------------------------|--|----------------------------|--|------------------------------------------------------------------------------------------------|--|
| TOLERANCE:<br>X.X ±0.30<br>X.XX ±0.25<br>X.XXX ±0.15<br><br>X.* ±2*    X.X* ±0.5*                        |  | DRAWN BY :<br><br>陈一鸣  |  | DATE :<br><br>2014-02-23   |  | PART NAME:<br><br>NGFF M.2 M KEY 1.5H 沉板0.5PH                                                  |  |
| <br>UNIT: mm [inch] |  | CHECKED BY:<br><br>马跃  |  | DATE :<br><br>2014-02-23   |  | PART NO.    HXCW13M-05NGFF-150B                                                                |  |
|                                                                                                          |  | APPROVED BY:<br><br>邱敏 |  | DATE :<br><br>2014-02-23   |  | MOLD NO.  |  |
| SCALE:1:1    SIZE: A4                                                                                    |  |                        |  | DRAW NO:    HYC-2309111105 |  | SHEET NO.    1 OF 1                                                                            |  |



|                                                                                                                             |                 |                                                                                                       |  |
|-----------------------------------------------------------------------------------------------------------------------------|-----------------|-------------------------------------------------------------------------------------------------------|--|
|  <div> <h1>深圳市华宇创精密电子有限公司</h1> </div>  |                 |                                                                                                       |  |
| <b>TOLERANCE:</b><br>X.X $\pm 0.30$<br>X.XX $\pm 0.25$<br>X.XXX $\pm 0.15$<br><br>X* $\pm 2^{\circ}$ X.X* $\pm 0.5^{\circ}$ |                 | <b>DRAWN BY :</b> 陈一鸣 <b>DATE :</b> 2014-02-23<br><br><b>CHECKED BY:</b> 马跃 <b>DATE :</b> 2014-02-23  |  |
| <br><b>UNIT:</b> mm [inch]             |                 | <b>PART NAME:</b> NGFF M.2 M KEY 1.5H 沉板 0.5PH<br><br><b>PART NO.</b> HYCW13M-05NGFF-150B             |  |
|                                                                                                                             |                 | <b>MOLD NO.</b>  |  |
| <b>APPROVED BY:</b> 邱敏 <b>DATE :</b> 2014-02-23                                                                             |                 | <b>DRAW NO:</b> HYC-2309111105<br><br><b>SHEET NO.</b> 1 OF 1                                         |  |
| <b>SCALE: 1:1</b>                                                                                                           | <b>SIZE: A4</b> |                                                                                                       |  |



|          |            |
|----------|------------|
| 1400     | 8400       |
| PCS/REEL | PCS/CARTON |



深圳市华宇创精密电子有限公司

|                                                                                                                                                                                                                                    |              |            |            |        |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------|------------|------------|--------|
| <p>TOLERANCE:</p> <p>X.X <math>\pm 0.30</math></p> <p>X.XX <math>\pm 0.25</math></p> <p>X.XXX <math>\pm 0.15</math></p> <p>X' <math>\pm 2'</math> X.X' <math>\pm 0.5'</math></p> <p>UNIT: mm [inch]</p> <p>SCALE: 1:1 SIZE: A4</p> | DRAWN BY:    | DATE:      | PART NAME: |        |
|                                                                                                                                                                                                                                    | 陈一鸣          | 2014-02-23 | 包装图        |        |
|                                                                                                                                                                                                                                    | CHECKED BY:  | DATE:      | PART NO.   |        |
|                                                                                                                                                                                                                                    | 马跃           | 2014-02-23 | MOLD NO.   |        |
|                                                                                                                                                                                                                                    | APPROVED BY: | DATE:      | DRAW NO:   |        |
|                                                                                                                                                                                                                                    | 邱敏           | 2014-02-23 | SHEET NO.  | 1 OF 1 |