



**Part Number :** [2064621100](#)  
**Product Description :** Micro-Fit+ Terminal  
Position Assurance (TPA) Retainer, 11 Circuits,  
3.00mm Pitch, UL 94V-0, Glow-Wire Capable,  
Natural  
**Series Number :** 206462  
**Status :** Active  
**Product Category :** Connector Accessories



## Documents & Resources

### Drawings

[2064621100\\_sd.pdf](#)  
[2064620000-PK-000.pdf](#)

### 3D Models and Design Files


[2064621100\\_stp.zip](#)

### Specifications

[2064600001-AS-000.pdf](#)  
[2064600000-PS-000.pdf](#)  
[2159530000-PS-000.pdf](#)  
[2064600000-TS-000.pdf](#)  
[2064600001-TS-000.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC

- Low-Halogen

#### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### EU RoHS Certificate of Compliance

---

### Part Details

#### General

Status	Active
Category	Connector Accessories
Series	206462
Description	Micro-Fit+ Terminal Position Assurance (TPA) Retainer, 11 Circuits, 3.00mm Pitch, UL 94V-0, Glow-Wire Capable, Natural
Component Type	Terminal Position Assurance
Product Name	Micro-Fit+
UPC	191130009152

#### Agency

UL	E29179
----	--------

#### Physical

Circuits (Loaded)	11
Circuits (maximum)	11
Color - Resin	Natural
Flammability	94V-0
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	0.202/g
Number of Rows	1
Packaging Type	Bag
Temperature Range - Operating	-40° to +125°C

---

Use with Part(s)

Description	Part Number
Micro-Fit+ Dual Row Receptacle Housings	<u>206461</u>
Micro-Fit+ Dual Row Plug Housings	<u>215922</u>

---