

HC-STA-D50-BCSFD-PL-BK - Protective cover

1424417

<https://www.phoenixcontact.com/us/products/1424417>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Protective cover D50, for double locking latch, protective cover material: PA, height: 19 mm, seal: no, Standard



Commercial data

Item number	1424417
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF66
Product key	BF7AZC
Catalog page	Page 532 (C-2-2019)
GTIN	4055626371573
Weight per piece (including packing)	40.7 g
Weight per piece (excluding packing)	40.7 g
Customs tariff number	85389099
Country of origin	CN

HC-STA-D50-BCSFD-PL-BK - Protective cover

1424417

<https://www.phoenixcontact.com/us/products/1424417>



Technical data

Notes

General	Protective cover for supporting base element with double locking latch
---------	--

Product properties

Product type	Protective cover
Housing type	Protective cover
Application	Standard
Type	D50
Type	for supporting base element with double locking latch
Seal present	no

Data management status

Article revision	01
------------------	----

Dimensions

Dimensional drawing	
Width	60.5 mm
Height	19 mm
Length	86.5 mm

Material specifications

Material Protective cover	PA
Flammability rating according to UL 94	V0
Material, protective cover	PA

Mechanical properties

Mechanical data	
Locking type	Pin

Environmental and real-life conditions

Ambient conditions	
Degree of protection	IP66
Ambient temperature (operation)	-20 °C ... 100 °C

Mounting

Assembly note	Plastic protective cover for short-term protection
---------------	--

HC-STA-D50-BCSFD-PL-BK - Protective cover


1424417

<https://www.phoenixcontact.com/us/products/1424417>



Drawings

Dimensional drawing



Dimensional drawing

Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1424417>

DNV

Approval ID: TAE000037S



EAC

Approval ID: EAC-Zulassung

Classifications

ECLASS

ECLASS-11.0	27440208
ECLASS-12.0	27440208
ECLASS-13.0	27440208

ETIM

ETIM 9.0	EC002314
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

HC-STA-D50-BCSFD-PL-BK - Protective cover

1424417

<https://www.phoenixcontact.com/us/products/1424417>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com