

Han TC70-HMC-FC-CRT-6 mm²-AU



Image is for illustration purposes only. Please refer to product description.

Part number	09 11 200 6230
Specification	Han TC70-HMC-FC-CRT-6 mm²-AU
HARTING eCatalogue	https://b2b.harting.com/09112006230

Identification

Category	Contacts
Series	TC 70
Type of contact	Crimp contact

Version

Gender	Female
Manufacturing process	Turned contacts

Technical characteristics

Conductor cross-section	6 mm²
Rated current	≤70 A
Contact resistance	≤0.3 mΩ
Stripping length	15 mm
Limiting temperature	-40 ... +125 °C
Mating cycles with other HMC components	≥10,000

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	HMC gold plated

Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
----------------	--------------------------



Pushing Performance
Since 1945

Commercial data

Packaging size	10
Net weight	7.4 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140188167
ETIM	EC000796
eCl@ss	27440204 Contact for industrial connectors