





- Series 180, 182, and 183 DIL Headers are equipped with solder cups for wiring applications.
- Series 180 terminations are pluggable 0,51 dia. solder tails MM #8000, See page 183 for details. Series 182 and 183 terminations are two or three level wrapposts MM #8301. See page 194 for details.
- Insulators are high temperature thermoplastic.



Total number of pins				Quantity per tube	For Electrical, Mechanical & Enviromental Data, See pg. 4 Ordering Information RoHS 2002/95/EC		
	A	B	C		Solder Tail	2 Level Wrapost L = 9,4	3 Level Wrapost L = 12,95
10	12,6	5,08	7,6	41	180-10-210-00-001000	182-10-210-00-001000	183-10-210-00-001000
4	5,0	7,62	10,1	102	180-10-304-00-001000	182-10-304-00-001000	183-10-304-00-001000
6	7,6	7,62	10,1	67	180-10-306-00-001000	182-10-306-00-001000	183-10-306-00-001000
8	10,1	7,62	10,1	50	180-10-308-00-001000	182-10-308-00-001000	183-10-308-00-001000
10	12,6	7,62	10,1	40	180-10-310-00-001000	182-10-310-00-001000	183-10-310-00-001000
14	17,7	7,62	10,1	28	180-10-314-00-001000	182-10-314-00-001000	183-10-314-00-001000
16	20,3	7,62	10,1	25	180-10-316-00-001000	182-10-316-00-001000	183-10-316-00-001000
18	22,8	7,62	10,1	22	180-10-318-00-001000	182-10-318-00-001000	183-10-318-00-001000
20	25,3	7,62	10,1	20	180-10-320-00-001000	182-10-320-00-001000	183-10-320-00-001000
22	27,8	7,62	10,1	18	180-10-322-00-001000	182-10-322-00-001000	183-10-322-00-001000
24	30,4	7,62	10,1	16	180-10-324-00-001000	182-10-324-00-001000	183-10-324-00-001000
28	35,5	7,62	10,1	14	180-10-328-00-001000	182-10-328-00-001000	183-10-328-00-001000
20	25,4	10,16	12,7	20	180-10-420-00-001000	182-10-420-00-001000	183-10-420-00-001000
22	27,8	10,16	12,7	18	180-10-422-00-001000	182-10-422-00-001000	183-10-422-00-001000
24	30,4	10,16	12,7	16	180-10-424-00-001000	182-10-424-00-001000	183-10-424-00-001000
28	35,5	10,16	12,7	14	180-10-428-00-001000	182-10-428-00-001000	183-10-428-00-001000
32	40,6	10,16	12,7	12	180-10-432-00-001000	182-10-432-00-001000	183-10-432-00-001000
24	30,4	15,24	17,7	16	180-10-624-00-001000	182-10-624-00-001000	183-10-624-00-001000
28	35,5	15,24	17,7	14	180-10-628-00-001000	182-10-628-00-001000	183-10-628-00-001000
32	40,6	15,24	17,7	12	180-10-632-00-001000	182-10-632-00-001000	183-10-632-00-001000
36	45,7	15,24	17,7	11	180-10-636-00-001000	182-10-636-00-001000	183-10-636-00-001000
40	50,8	15,24	17,7	10	180-10-640-00-001000	182-10-640-00-001000	183-10-640-00-001000
42	53,3	15,24	17,7	9	180-10-642-00-001000	182-10-642-00-001000	183-10-642-00-001000
48	60,9	15,24	17,7	8	180-10-648-00-001000	182-10-648-00-001000	183-10-648-00-001000
50	63,5	15,24	17,7	8	180-10-650-00-001000	182-10-650-00-001000	183-10-650-00-001000
52	66,0	15,24	17,7	7	180-10-652-00-001000	182-10-652-00-001000	183-10-652-00-001000
50	63,5	22,86	25,3	8	180-10-950-00-001000	182-10-950-00-001000	183-10-950-00-001000
52	66,0	22,86	25,3	7	180-10-952-00-001000	182-10-952-00-001000	183-10-952-00-001000
64	81,2	22,86	25,3	6	180-10-964-00-001000	182-10-964-00-001000	183-10-964-00-001000
For RoHS compliance select plating code. SPECIFY PLATING CODE XX= 10					Pin Plating	0,25µm Au	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[183-10-964-00-001000](#) [183-10-952-00-001000](#) [183-10-950-00-001000](#) [183-10-652-00-001000](#) [183-10-650-00-001000](#) [183-10-648-00-001000](#) [183-10-642-00-001000](#) [183-10-640-00-001000](#) [183-10-636-00-001000](#) [183-10-632-00-001000](#) [183-10-628-00-001000](#) [183-10-624-00-001000](#) [183-10-432-00-001000](#) [183-10-428-00-001000](#) [183-10-424-00-001000](#) [183-10-422-00-001000](#) [183-10-420-00-001000](#) [183-10-328-00-001000](#) [183-10-324-00-001000](#) [183-10-322-00-001000](#) [183-10-320-00-001000](#) [183-10-318-00-001000](#) [183-10-316-00-001000](#) [183-10-314-00-001000](#) [183-10-310-00-001000](#) [183-10-308-00-001000](#) [183-10-306-00-001000](#) [183-10-304-00-001000](#) [183-10-210-00-001000](#) [182-10-964-00-001000](#) [182-10-952-00-001000](#) [182-10-950-00-001000](#) [182-10-652-00-001000](#) [182-10-650-00-001000](#) [182-10-648-00-001000](#) [182-10-642-00-001000](#) [182-10-640-00-001000](#) [182-10-636-00-001000](#) [182-10-628-00-001000](#) [182-10-624-00-001000](#) [182-10-432-00-001000](#) [182-10-428-00-001000](#) [182-10-424-00-001000](#) [182-10-422-00-001000](#) [182-10-420-00-001000](#) [182-10-328-00-001000](#) [182-10-324-00-001000](#) [182-10-322-00-001000](#) [182-10-320-00-001000](#) [182-10-318-00-001000](#) [182-10-316-00-001000](#) [182-10-314-00-001000](#) [182-10-310-00-001000](#) [182-10-308-00-001000](#) [182-10-306-00-001000](#) [182-10-304-00-001000](#) [182-10-210-00-001000](#) [180-10-964-00-001000](#) [180-10-952-00-001000](#) [180-10-950-00-001000](#) [180-10-652-00-001000](#) [180-10-650-00-001000](#) [180-10-648-00-001000](#) [180-10-642-00-001000](#) [180-10-640-00-001000](#) [180-10-636-00-001000](#) [180-10-632-00-001000](#) [180-10-628-00-001000](#) [180-10-624-00-001000](#) [180-10-432-00-001000](#) [180-10-428-00-001000](#) [180-10-424-00-001000](#) [180-10-422-00-001000](#) [180-10-420-00-001000](#) [180-10-328-00-001000](#) [180-10-324-00-001000](#) [180-10-322-00-001000](#) [180-10-320-00-001000](#) [180-10-318-00-001000](#) [180-10-316-00-001000](#) [180-10-314-00-001000](#) [180-10-310-00-001000](#) [180-10-308-00-001000](#) [180-10-304-00-001000](#) [180-10-210-00-001000](#)