




DESCRIPTION: DSUB IP67 FLANGE // FEMALE // COMBO // RIGHT ANGLE PIN PCB MOUNT



HARDWARE OPTIONS



NOTE:

MATERIAL

HOUSING
FLANGE
CONTACT
SHELL
O-RING
SEALING COMPOUND
HARDWARE

PBT UL94V-0, BLACK
PBT UL94V-0, BLACK
BRASS, PLATING P/N KEY BELOW
STEEL, NICKEL
SILICONE
EPOXY
BRASS: NICKEL PLATED

ELECTRICAL

SIGNAL CONTACT RATED CURRENT	5A
POWER CONTACT RATED CURRENT	P/N KEY BELOW
VOLTAGE	1000 VAC 1 MIN
INSULATOR RESISTANCE	5 Gohms MIN.
SIGNAL CONTACT RESISTANCE	10 mOhms MAX.
POWER CONTACT RESISTANCE	2.0 mOhms MAX.
WATER PROOF	IP67

ENVIRONMENT

OPERATION TEMPERATURE -25°C TO $+85^{\circ}\text{C}$

CDFR13W3213LYYY

SERIES _____

 CDF = COMBO DSUB FLANGE

CONTACT TYPE _____

 R = RIGHT ANGLE PCB MOUNT

POSITION _____

 13W3

GENDER _____

 2 = FEMALE

POWER CONTACT AMPERAGE _____

 2 = 20 AMPS

 4 = 40 AMPS

HARDWARE OPTIONS _____

 1 = 4-40 THREADED INSERTS/4-40 JACKSCREWS

 6 = 4-40 THREADED BRACKETS &

 BOARD LOCKS/4-40 JACKSCREWS

CONTACT PLATING OPTIONS _____

 1 = GOLD FLASH

 2 = 30u" GOLD PLATING

UNITS = mm

DO NOT SCALE FROM DRAWING

DRAWN:
J. KADEL

DATE: 04/27/2020

TOLERANCES

X.	± 0.40
.X	± 0.30
.XX	± 0.20
.XXX	± 0.10

NorComp

SCALE: NTS

DWG NO.

SHEET	OF
1	2

CDFR13W3213LYYY

REV
1

NC

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NorComp:](#)

[CDFR13W3213L211](#) [CDFR13W3213L212](#) [CDFR13W3213L261](#) [CDFR13W3213L262](#) [CDFR13W3213L411](#)
[CDFR13W3213L412](#) [CDFR13W3213L461](#) [CDFR13W3213L462](#) [CDFR13W3113L262](#) [CDFR13W3113L411](#)
[CDFR13W3113L412](#) [CDFR13W3113L461](#) [CDFR13W3113L462](#) [CDFR13W3113L261](#) [CDFR13W3113L211](#)
[CDFR13W3113L212](#)