


PIN RECEPTACLES

FOR .015" - .025" DIAMETER PINS

8964

8964-0-15-XX-30-XX-04-0


Press-fit in .057 mounting hole



5342

5342-0-15-XX-35-XX-10-0


Solder mount in .051 min. mounting hole
Also available on 8mm wide carrier tape:
6,000 parts per 13" reel
Order as: 5342-0-57-XX-35-XX-10-0



8857

8857-X-15-XX-32-XX-04-0

Press-fit in .057 mounting hole




Basic Part Number	Length A
8857-0	.311
8857-1	.448
8857-2	.589
8857-3	.731
8857-4	.871

8862/8877

88XX-0-15-XX-30-XX-04-0

Press-fit in .056 mounting hole




Basic Part Number	Length A
8862-0	.300
8877-0	.350

1334

1334-0-15-XX-30-XX-04-0


Press-fit in .057 mounting hole



8855

8855-0-15-XX-30-XX-34-0


Press-fit in .057 mounting hole



2954

2954-0-18-XX-30-XX-10-0


Press-fit in .057 mounting hole
Accepts wire sizes up to .028" dia.



9363

9363-0-15-XX-35-XX-10-0


Solder mount in .057 min. mounting hole



1023

1023-0-15-XX-30-XX-04-0


Press-fit in .061 mounting hole



1701

1701-0-15-XX-30-XX-10-0

Press-fit in .057 mounting hole



SPECIFICATIONS:

Shell Material: Brass Alloy 360, 1/2 Hard

Contact Material: Beryllium Copper Alloy 172, HT

Dimensions: Inches

Tolerances On: Lengths: $\pm .005$

Diameters: $\pm .002$

Angles: $\pm 2^\circ$



ORDER CODE: XXXX - X - 1X - XX - XX - XX - 10 - 0

BASIC PART #

SPECIFY SHELL FINISH:

- 01 200 μ " TIN/LEAD OVER NICKEL
- ◆ 80 200 μ " TIN OVER NICKEL (RoHS)
- ◆ 15 10 μ " GOLD OVER NICKEL (RoHS)

SPECIFY CONTACT FINISH:

- 02 100 μ " TIN/LEAD OVER NICKEL
- ◆ 84 100 μ " TIN OVER NICKEL (RoHS)
- ◆ 27 30 μ " GOLD OVER NICKEL (RoHS)

SELECT CONTACT:

#30, #32 or #35 CONTACT (DATA ON PAGE 253 & 254)
(For alternate contact choices, see groups B and C on page 248)



Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[8964-0-15-01-30-02-04-0](#) [8964-0-15-01-30-27-04-0](#) [8877-0-15-01-30-02-04-0](#) [8862-0-15-01-30-27-04-0](#) [8857-4-15-01-32-02-04-0](#) [8857-4-15-01-32-27-04-0](#) [8857-3-15-01-32-02-04-0](#) [8857-2-15-01-32-27-04-0](#) [8857-1-15-01-32-02-04-0](#) [8857-0-15-01-32-02-04-0](#) [8857-0-15-01-32-27-04-0](#) [8877-0-15-80-30-27-04-0](#) [8857-4-15-80-32-84-04-0](#) [8857-4-15-80-32-27-04-0](#) [8857-3-15-80-32-84-04-0](#) [8857-2-15-80-32-27-04-0](#) [8857-1-15-80-32-84-04-0](#) [8857-1-15-80-32-27-04-0](#) [8857-0-15-80-32-84-04-0](#) [8857-0-15-80-32-27-04-0](#) [8857-3-15-15-32-27-04-0](#) [8877-0-15-15-30-27-04-0](#)