



Pushing Performance
Since 1945

Han-Modular coax F-contact 75Ohm (RG179)



Image is for illustration purposes only. Please refer to product description.

Part number	09 14 000 6221
Specification	Han-Modular coax F-contact 75Ohm (RG179)
HARTING eCatalogue	https://b2b.harting.com/09140006221

Identification

Category	Contacts
Series	DIN 41626 har-modular®
Type of contact	Coaxial contact
Description of the contact	for cables RG 179 BU, 187 AU

Version

Termination method	Solder/crimp termination
Gender	Female
Manufacturing process	Turned contacts

Technical characteristics

Rated current	≤1.5 A
Contact resistance	≤10 mΩ
Impedance	75 Ω

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Gold plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50



Pushing Performance
Since 1945

Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	b51e5b97-eeb5-438b-8538-f1771d43c17d
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel

Specifications and approvals

Specifications	IEC 60664-1
	IEC 61984

Commercial data

Packaging size	10
Net weight	2.58 g
Country of origin	Hungary
European customs tariff number	85366990
GTIN	5713140572928
eCl@ss	27440204 Contact for industrial connectors