


SERIES

M1330



Unshielded Surface Mount Inductors



Actual Size

Military QPL Approval

- M83446/23 Phenolic Core
- M83446/24 Iron Core
- M83446/25 Ferrite Core

† **Ordering Note** Military parts must be ordered to the M83446/ part number

Physical Parameters

	Inches	Millimeters
A	0.300 to 0.320	7.62 to 8.13
B	0.105 to 0.125	2.67 to 3.18
C	0.125 to 0.145	3.18 to 3.68
D	0.020 to 0.040	0.51 to 1.02
E	0.075 to 0.095	1.91 to 2.41
F	0.230 to 0.260	5.84 to 6.60

Dimensions "A" & "C" are over terminals

Weight Max (Grams) 0.30

Operating Temperature Range

Phenolic: -55°C to +125°C
 Iron and Ferrite: -55°C to +105°C

Current Rating at 90°C Ambient

Phenolic: 35°C Rise
 Iron and Ferrite: 15°C Rise

Maximum Power Dissipation at 90°C Ambient

Phenolic: 0.210 W
 Iron: 0.090 W
 Ferrite: 0.073 W

Marking

Delevan; dash number; date code (YYWWL) followed by an M.
 Example: M1330-42K
 DELEVAN
 42
 1322A M

Packaging Tape & reel (16mm): 7" reel, 500 pieces max.;
 13" reel, 2200 pieces max.

Made In the U.S.A.

DASH NUMBER*	MIL DASH #	INDUCTANCE (µH) ±10%	TEST FREQUENCY (MHz)	Q MINIMUM	SRF MINIMUM (MHz)	DC RESISTANCE MAXIMUM (OHMS)	CURRENT RATING MAXIMUM (mA)
--------------	------------	----------------------	----------------------	-----------	-------------------	------------------------------	-----------------------------

M83446/23 – SERIES M1330 PHENOLIC CORE							
-94K	01F	0.10	40	25.0	680.0	0.08	1380
-96K	02F	0.12	40	25.0	640.0	0.09	1300
-00K	03F	0.15	38	25.0	600.0	0.10	1230
-02K	04F	0.18	35	25.0	550.0	0.12	1120
-04K	05F	0.22	33	25.0	510.0	0.14	1040
-06K	06F	0.27	33	25.0	430.0	0.16	975
-08K	07F	0.33	30	25.0	410.0	0.22	830
-10K	08F	0.39	30	25.0	365.0	0.30	710
-12K	09F	0.47	30	25.0	330.0	0.35	660
-14K	10F	0.56	30	25.0	300.0	0.50	550
-16K	11F	0.68	28	25.0	275.0	0.60	500
-18K	12F	0.82	28	25.0	250.0	0.85	420
-20K	13F	1.00	25	25.0	230.0	1.00	390
M83446/24 – SERIES M1330 IRON CORE							
-22K	01F	1.20	25	7.9	150.0	0.18	620
-24K	02F	1.50	28	7.9	140.0	0.22	560
-26K	03F	1.80	30	7.9	125.0	0.30	480
-28K	04F	2.20	30	7.9	115.0	0.40	415
-30K	05F	2.70	37	7.9	100.0	0.55	355
-32K	06F	3.30	45	7.9	90.0	0.85	285
-34K	07F	3.90	45	7.9	80.0	1.00	263
-36K	08F	4.70	45	7.9	75.0	1.20	239
-38K	09F	5.60	50	7.9	65.0	1.80	195
-40K	10F	6.80	50	7.9	60.0	2.00	185
-42K	11F	8.20	55	7.9	55.0	2.70	160
-44K	12F	10.00	55	7.9	50.0	3.30	144
-46K	13F	12.0	45	2.5	40.0	2.70	160
-48K	14F	15.0	45	2.5	35.0	2.80	157
-50K	15F	18.0	45	2.5	30.0	3.10	149
-52K	16F	22.0	45	2.5	25.0	3.30	144
-54K	17F	27.0	45	2.5	20.0	3.50	140
M83446/25 – SERIES M1330 FERRITE CORE							
-56K	01F	33.0	35	2.5	24.0	3.40	130
-58K	02F	39.0	35	2.5	22.0	3.60	125
-60K	03F	47.0	35	2.5	20.0	4.50	110
-62K	04F	56.0	35	2.5	18.0	5.70	100
-64K	05F	68.0	35	2.5	15.0	6.70	92
-66K	06F	82.0	35	2.5	14.0	7.30	88
-68K	07F	100.0	35	2.5	13.0	8.00	84
-70K	08F	120.0	30	0.79	12.0	13.00	66
-72K	09F	150.0	30	0.79	11.0	15.00	61
-74K	10F	180.0	30	0.79	10.0	17.00	57
-76K	11F	220.0	30	0.79	9.0	21.00	52
-78K	12F	270.0	30	0.79	8.0	25.00	47
-80K	13F	330.0	30	0.79	7.0	28.00	45
-82K	14F	390.0	30	0.79	6.5	35.00	40
-84K	15F	470.0	30	0.79	6.0	42.00	36
-86K	16F	560.0	30	0.79	5.0	46.00	35
-88K	17F	680.0	30	0.79	4.2	60.00	30
-90K	18F	820.0	30	0.79	3.8	65.00	29
-92K	19F	1000.0	30	0.79	3.4	72.00	28

Parts listed above are QPL/MIL qualified

*Complete part # must include series # PLUS the dash #



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Delevan:](#)

[M1330-92K](#) [M1330-44K](#) [M1330-20K](#) [M1330-28K](#) [M1330-94K](#) [M1330-96K](#) [M1330-90K](#) [M1330-56K](#) [M1330-40K](#)
[M1330-74K](#) [M1330-38K](#) [M1330-76K](#) [M1330-24K](#) [M1330-04K](#) [M1330-58K](#) [M1330-34K](#) [M1330-62K](#) [M1330-22K](#)
[M1330-46K](#) [M1330-64K](#) [M1330-84K](#) [M1330-16K](#) [M1330-14K](#) [M1330-82K](#) [M1330-10K](#) [M1330-78K](#) [M1330-80K](#)
[M1330-08K](#) [M1330-02K](#) [M1330-42K](#) [M1330-72K](#) [M1330-60K](#) [M1330-70K](#) [M1330-52K](#) [M1330-36K](#) [M1330-50K](#)
[M1330-86K](#) [M1330-06K](#) [M1330-18K](#) [M1330-48K](#) [M1330-54K](#) [M1330-26K](#) [M1330-30K](#) [M1330-88K](#) [M1330-32K](#)
[M1330-68K](#) [M1330-00K](#) [M1330-12K](#) [M1330-66K](#)