

RC-Z2301 - Metal protective cap



1604420

<https://www.phoenixcontact.com/us/products/1604420>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Metal protective cap, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1241780

Commercial data

Item number	1604420
Packing unit	250 pc
Minimum order quantity	250 pc
Note	Made to order (non-returnable)
Sales key	AB36
Product key	ABRGAB
GTIN	4046356249256
Weight per piece (including packing)	16.44 g
Weight per piece (excluding packing)	16.44 g
Customs tariff number	74198090
Country of origin	DE

RC-Z2301 - Metal protective cap



1604420

<https://www.phoenixcontact.com/us/products/1604420>

Technical data

Product properties

Product type	Cable clamp type cage
--------------	-----------------------

RC-Z2301 - Metal protective cap



1604420

<https://www.phoenixcontact.com/us/products/1604420>

Classifications

ECLASS

ECLASS-11.0	27440312
ECLASS-13.0	27440312
ECLASS-12.0	27440312

ETIM

ETIM 9.0	EC002641
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

RC-Z2301 - Metal protective cap



1604420

<https://www.phoenixcontact.com/us/products/1604420>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)
China RoHS	
Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	4b96a2f9-95b7-4d39-9873-3edacfd45421

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com