



Part Number : 936000493

Product Description : GWconnect Turned Crimp Contact for 10A Inserts and Modules, Female, Silver (Ag) Plated Copper Alloy, 0.50mm² (20 AWG), 100 per Bag

Series Number : 93601

Status : Active

Product Category : Heavy-Duty Contacts

Engineering Number : 7100.4202.0



Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	☒
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Heavy-Duty Contacts
Series	93601
Description	GWconnect Turned Crimp Contact for 10A Inserts and Modules, Female, Silver (Ag) Plated Copper Alloy, 0.50mm ² (20 AWG), 100 per Bag
Contact Type	Turned Crimp
Product Family	GWconnect Heavy Duty Connectors (HDC)
Product Name	GWconnect
UPC	887191866192

Agency

CSA	256883
UL	E249674

Electrical

Current - Maximum per Contact	10.0A
-------------------------------	-------

Physical

Gender	Female
Material - Contact	Copper Alloy
Material - Plating	Silver
Net Weight	0.700/g
Number of Grooves	0
Packaging Type	Bag
Stripping Length	8.00mm
Wire Size (AWG)	20
Wire Size mm ²	0.50

Mates With / Use With

Mates with Part(s)

Description	Part Number
GWconnect Heavy-Duty Connectors and Accessories	<u>93601</u>

Use with Part(s)

Description	Part Number
Use With	S-D, S-DD, S-K, S-Q, S-QD, and S-M Inserts

This document was generated on Oct 14, 2024