


DESCRIPTION: CONNECTOR FOR 988 SERIES BACK SHELL KIT





No. OF PINS	DIMENSIONS		
	A	B	C
50	1.545 [39.30]	1.372 [34.85]	0.366 [9.30]
68	1.989 [50.60]	1.825 [46.35]	0.366 [9.30]

ASSEMBLY VERSION

MATERIAL:
HOUSING: THREMOPLASTIC, BLACK, P.B.T. UL94V-0
CONTACTS: PHOSPHOR BRONZE, GOLD SELECTIVE PLATED
FRONT SHELL: STEEL, NICKEL PLATED OVER COPPER



ELECTRICAL:
CURRENT RATING: 0.5 AMPS
INSULATOR RESISTANCE: 500 MEGOHMS Min.
DIELECTRIC WITHSTANDING: 500VAC
CONTACT RESISTANCE: 35MilliOhms Max.
OPERATING TEMPERATURE: -55° ~ +85° C



CONNECTOR PART NUMBER
113-YYY-103L001

SERIES
POSITIONS
050
068
GENDER
1 = MALE
TERMINATION
0 = SOLDER
SHELL PLATING
3 = NICKEL PLATED
RoHS COMPLIANT
L = LOW TEMP. PROCESS
HARDWARE OPTIONS
00 = NO HARDWARE
PLATING OPTIONS
1 = GOLD FLASH

DO NOT SCALE FROM DRAWING

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: C. SMITH		DATE: 04-18-08		
		CHECKED:		DATE:		
			SCALE: 2 : 1	SHEET 1	OF 1	REV 3
			DWG NO. 113-YYY-103L001			

RoHS COMPLIANT

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

NorComp:

[113-050M103L001](#) [113-068M103L001](#)