




**Part Number :** 936010470  
**Product Description :** GWconnect Turned Crimp Contact for 70A Female S-M70/2 Inserts, Silver (Ag) Plated Copper Alloy, 10.00mm<sup>2</sup> (7 AWG), 100 per Bag  
**Series Number :** 93601  
**Status :** Active  
**Product Category :** Heavy-Duty Contacts  
**Engineering Number :** 7700.3184.0



## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

## Part Details

### General

Status	Active
Category	Heavy-Duty Contacts
Series	93601
Description	GWconnect Turned Crimp Contact for 70A Female S-M70/2 Inserts, Silver (Ag) Plated Copper Alloy, 10.00mm <sup>2</sup> (7 AWG), 100 per Bag
Contact Type	Turned Crimp
Product Family	GWconnect Heavy Duty Connectors (HDC)
Product Name	GWconnect
UPC	887191892283

## Electrical

Current - Maximum per Contact	70.0A
-------------------------------	-------

## Physical

Gender	Female
Material - Contact	Copper Alloy
Material - Plating	Silver
Net Weight	7.000/g
Number of Grooves	0
Packaging Type	Bag
Stripping Length	15.00mm

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
GWconnect Heavy-Duty Connectors and Accessories	<u>93601</u>

### Use with Part(s)

Description	Part Number
Use With	Female S-M70/2 Inserts

---



---

This document was generated on Oct 14, 2024