

Han 3HPR Hood cover,toggle lock,powder c




Image is for illustration purposes only. Please refer to product description.

Part number	09 40 703 5404
Specification	Han 3HPR Hood cover,toggle lock,powder c
HARTING eCatalogue	https://b2b.harting.com/09407035404

Identification

Category	Accessories
Series of hoods/housings	Han [®] HPR
Type of accessory	Protection cover
Description of the accessory	for hoods With fixing cord

Version

Size	3 A
Locking type	Toggle locking

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65 IP68
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR
RoHS	compliant



Pushing Performance
Since 1945

Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel
	Naphthalene

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
	CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	DNV GL

Commercial data

Packaging size	10
Net weight	43.26 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140191921
ETIM	EC002314
eCl@ss	27440208 Cap for industrial connectors